



DATE	REV	DESCRIPTION	BY	CHKD
12/9	A/0	NEW	WZY	YZG



50MM


NPC-1110
10FT CAT5E BLACK MOLDED ,
SNAGLESS PATCH CABLE ,
QTY : 1

條 碼
800118003517

ROHS
Made in China

30MM

Conductor	Bare Copper 24AWG 70.196±0.015mm
Insulation	Thickness:MIN at any point 0.15mm MAX AVG 0.25mm Diameter 0.98±0.06mm
Jacket	PVC Thickness:MIN at any point 0.42mm MAX AVG 0.48mm Diameter 5.44±0.2mm
WIRE	CAT.5E UTP STR 24AWG*4P
PLUG	MOLDING YUS-04 8P8C 3u
Length	xxFT
COLOR	SEE: ② BLACK BLUE RED YELLOW GREEN WHITE GRAY ORANGE



PINOUT			
PA/R	P1 (T568B)	WIRE	P2 (T568B)
1	1	WHT/ORG	1
	2	ORG	2
2	3	WHT/GRN	3
	6	GRN	6
3	4	BLU	4
	5	WHT/BLU	5
4	7	WHT/BRN	7
	8	BRN	8

②

COLOR	x	Marking
BLACK	1	QUEST CABLE SOLUTIONS NWR-1151 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT
BLUE	2	QUEST CABLE SOLUTIONS NWR-1150 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT
RED	3	QUEST CABLE SOLUTIONS NWR-1153 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT
YELLOW	5	QUEST CABLE SOLUTIONS NWR-1155 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT
GREEN	6	QUEST CABLE SOLUTIONS NWR-1156 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT
WHITE	8	QUEST CABLE SOLUTIONS NWR-1154 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT
GRAY	9	QUEST CABLE SOLUTIONS NWR-1159 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT
ORANGE	4	QUEST CABLE SOLUTIONS NWR-1154 CAT5e ENHANCED 350MHZ PATCH ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2 3P VERIFIED 24AWG2P TYPE CM(L) C(L) CMR E164469-F3 3X000PT

①

ITEM	Length
NPC-1x01X	1FT
NPC-1x03X	3FT
NPC-1x07X	7FT
NPC-1x15X	15FT
NPC-1x25X	25FT

Unless specified on the drawing, tolerances are per the follows:	
.x	± 1
.XX	± 0.2
	± 0.05
3RD	

DRAW.NO	00157	ITEM	SEE: ①	
DEPARTMENT		DRAW	WZY	DATE 2008/12/9
SCALE		CHECKER		APPROVAL
UNIT	MM	SHEET	1 OF 1	

Test Temperature: 20°C