

[Skip to content](#)

[Corporate Home](#) | [Electronic Components](#) | [Segments](#) | [Who We Are](#)

Worldwide



Our commitment. Your advantage.

Search

By:



[Sign In](#) | [Register](#) ([Why Register?](#))

[Products](#)



- Connectors
- Electromechanical Components
- Electronic Modules
- Fiber Optics
- Filters
- Identification Labeling Products
- Passive Components
- Power Sources
- RF & Microwave Products
- Tooling Products
- Touch Screen Displays
- Tubing, Molded and Harnessing Products
- Wire, Cable and Cable Assemblies
- List all Product Types

Aerospace & Defense

Appliance

Automotive

Communications

Computer & Consumer Electronics

Industrial & Commercial

Instrumentation & Medical Equipment

By Brand

A to Z

Documentation

Find Documents & Drawings

Find CAD Models

SPICE/Electrical Models

NAFTA Certificate of Origin

White Papers

Resources

RoHS Compliance & Alternates

Cross Reference Products

Compare Multiple Products

Check Distributor Inventory

Find Authorized Distributors

My Account

Sign In

Register

Customer Support

Support

RoHS Support Center

Glossary of Terms

eBulletin Newsletter

[Home](#) > [Products](#) > [By Type](#) > [Switches](#) > [Product Feature Selector](#) > Product Details

1825258-2 Product Details

http://catalog.tycoelectronics.com/TE/bin/TE.Connect?C=1&M=BYPN&TCPN=1825258-2&RQPN=MSS1200GR04 (2 of 4)27/09/2007 09:34:34 •



1825258-2
(MSS1200GR04)



[Active](#)

Slide Switches



[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Number of Positions = 2
- Single Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Side
- Actuator Color = Black
- MSS Series

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH, MSS 1200R SERIES, SP-DT, RIGHT ANGLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)**Product Type Features:**

- [Number of Positions](#) = 2
- Configuration (Pole-Throw) = Single Pole - Double Throw
- Actuator Style = Side
- Mount Angle = Vertical
- Grade = Instrumentation
- Termination Type = PC
- PCB Retention Feature = Yes

Electrical Characteristics:

- Contact Rating = 300mA

Body Related Features:

- Actuator Color = Black
- Series = MSS
- Mount Style = Through-Hole
- Switch Style = Low Profile
- PCB Tail Length (mm [in]) = 3.68 [0.145]
- PCB Retention Method = Guide Posts
- Actuator Length (mm [in]) = 3.99 [0.157]
- Actuator Material = POM
- Flammability Rating = UL 94-HB
- Actuator Travel = 2.00 [.079]

Contact Related Features:

- Contact Plating = Gold
- Contact Material = Copper Alloy

Configuration Related Features:

- Terminal Configuration = Standard
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© [2007 Tyco Electronics Corporation All Rights Reserved](#)