



HIRSCHMANN

A BELDEN BRAND

Product information N11R EF


Industrial Connecting Solutions: Circular Connectors: MIL, DIN, Universal Connectors: DIN 43651 Connectors (NR series): Straight cable socket: N11R EF

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256284-24367-24368-36227/en/conf/ui/state>

Name		N11R EF
		
		Straight cable socket, strain relief by means of a clamping cage
Delivery informations		
Availability		available
Product description		
Description		Straight cable socket, strain relief by means of a clamping cage
Type		N11R EF
Order No.		932 630-106
Type of contact		female
Number of contacts		11 + PE
Cable gland		PG 11
Cable diameter		8 mm to 10 mm
Conductor size		max. 0.5 mm ²
Standard		DIN 43651
Housing Color		grey
Technical data		
Pin dimensions		1.6 mm
Rated voltage		AC/DC 60 V
Rated current		5 A
Contact resistance		<= 5 mOhm
Type of termination		crimp
Suitable cables		0.14 mm ² to 0.5 mm ²
Material		
Contact surface material		Ag
Contact bearer material		PET
Housing material		PET
Environmental conditions		
Protection class (IEC 60529)		IP 65
Temperature range		-40 °C to +90 °C
Packaging unit		
Packaging unit		10 pieces
Scope of delivery and accessories		
Scope of delivery		1 cable sockets, not assembled, in polythene bag, with assembly instructions
Accessories to order separately		can be plugged into N11R AM, N11R AM 5, contacts: RBC 162/1

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.