

MODULAR JACKS AND PLUGS: GLX Series

Right Angle Modular Jack

Product Features

0.570" Height
 Snap-In Board Retention Tabs
 Available in 4, 6, 8 and 10 Position Housings
 CSA/NRTL Certified File No. LR78160
 UL File No. E134345

Performance Specifications

Materials and Finish

Housing Material

PBT Thermoplastic, UL 94V-0 Rated

Contact Material

Phosphor Bronze

Electrical Characteristics

Insulation Resistance

500 Megohms Min.

Dielectric Withstanding Voltage

1000V RMS, 60Hz

Contact Resistance

20 milliohms Max.

Current Rating

1.5A

Voltage Rating

125V DC

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-			
Series		Shield Option	Positions & Contacts	Other Option

Series

GLX - Right Angle Modular Jack

Shield Options

A - Non-Shielded with Panel Stops
 N - Non-Shielded without Panel Stops

Number of Positions / Contacts

44 - 4 Positions / 4 Contacts
 64 - 6 Positions / 4 Contacts
 66 - 6 Positions / 6 Contacts

Other Option

Plating Option

Blank - Gold Flash
 50 - 50μ" Gold Plating

Color Option


Blank - Gray
 BLK - Black

Contact Kycon for High Temperature and Other Options

GLX Series

Dimensions in mm

GLX-A-44xx



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kycon:

[GLX-A-66-50](#) [GLX-N-64-50](#) [GLX-A-64-50](#) [GLX-N-1010M](#) [GLX-N-1010M-50](#) [GLX-A-44-50](#) [GLX-N-44](#) [GLX-N-66](#)
[GLX-N-64](#) [GLX-N-64M-BLK](#) [GLX-A-66](#) [GLX-A-64](#) [GLX-A-44](#) [GLX-N-44-50](#) [GLX-N-44M-50](#) [GLX-N-66M-50](#) [GLX-N-](#)
[66-50](#) [GLX-N-88M](#) [GLX-N-88M-50](#) [GLX-N-44M](#) [GLX-A-66-BLK](#) [GLX-N-64M-50](#) [GLX-N-66M](#) [GLX-N-64M](#) [GLX-S-](#)
[88M](#) [GLX-S-88M-50](#) [GLX-N-1010M-BLK](#) [GLX-N-88M-BLK](#) [GLX-S1-88M-BLK](#) [GLX-S1-62M-BLK](#) [GLX-S1-66M-50](#)
[GLX-S1-62M](#) [GLX-S1-64M-50](#) [GLX-S1-88M](#) [GLX-N-62M-BLK](#) [GLX-A-62-BLK](#) [GLX-S1-1010M](#) [GLX-N-62M](#) [GLX-N-](#)
[66M-BLK](#) [GLX-S-1010M-BLK](#) [GLX-S1-66M](#) [GLX-N-44-BLK](#) [GLX-S-88M-BLK](#) [GLX-N-64-BLK](#) [GLX-S1-62M-50](#) [GLX-](#)
[N-66-BLK](#) [GLX-N-64-50-BLK](#) [GLX-S1-88M-50](#) [GLX-S-1010M](#) [GLX-S1-64M](#) [GLX-A-62](#) [GLX-S1-64M-BLK](#) [GLX-S1-](#)
[1010M-50](#) [GLX-S1-66M-BLK](#) [GLX-N-62-BLK](#) [GLX-N-62](#) [GLX-N-62M-50](#) [GLX-S1-1010M-BLK](#) [GLX-A-64-BLK](#) [GLX-](#)
[S-1010M-50](#) [GLX-N-62-50](#) [GLX-A-44-BLK](#) [GLX-N-44M-BLK](#) [GLX-A-62-50](#) [GLX-S1-1010M-15](#) [GLXHT-N-66M-BLK](#)
[GLX-S-1010M-15](#) [GLXHT-N-66M](#)