




Rating	16A 125VAC, 10A 250VAC			Mounting Hole	
	20A 14VDC 10A 28VDC, 6A 14VT				
Contact Resistance	50m ohm Max.				
Insulation Resistance	DC 500V 100M ohm Min.				
Dielectric Strength	AC 1500V 1 minute				
Operation Temp.	-20°C ~ 85°C				
Switch Function	2P SPST ON-OFF				



MATERIAL:

Frame: Black, Nylon 66 (94-V2)

Actuator: Black, PC (94-V2)

Waterproof Rubber: Black, Silicone


Terminals: Silver plated, Copper alloy

Hot Stamping: None





Waterproof: IP65

Circuit Diagram

OFF



ON



RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 6/23/06

Rev. 1

Unit: mm

Checked By: GG

Title:

ROCKER SWITCH

CW P/N:

GRB112A802BB