

344 **0%**
 MERCURY

 SR1136SW (SR42)
 Watch Battery OEM
 Swiss Made


Technical Data Sheet

Specifications


Chemical system	Zinc / Monovalent Silver Oxide, low drain
Nominal Voltage	1,55 V
Capacity	105 mAh, Discharge over 10 kΩ at 20 °C to 1,2 V
Operating Temperature	0 °C – 60 °C
Self Discharge	Less than 5% per year at 20 °C
Weight	~1,45 g

Dimensions

(according IEC 60086-3)

 Diameter 11,60 mm (0,457")
 Height 3,60 mm (0,142")


Discharge Curve

 Constant Load 10 kΩ
 Starting Drain 156 µA
 Temperature 20 °C


Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the PSDS document related to that product or product family.

Rev. 344MF_OEM.02 2010/11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renata](#):

[344.TS 0% HG](#) [344.MP 0% HG](#)