


Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 6A/250VAC
- Contact resistance: 50m Ω max.
- Insulation resistance: 500VDC 100M Ω min.
- Dielectric strength: 1500VAC for 1 minute

Mechanical Specifications:

- Type: 6P, DPDT
- Circuit: On-On (103-4024), On-(On) (103-4025)
- Operational life cycles: 100,000

Note:

- RoHS Compliant

Toggle Switches
103-4024-EV, 103-4025-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[103-4024-EV](#) [103-4025-EV](#)