







REV. NO.		DATE	DESCRIPTION	DATE	APPRO.
8	BD	39	0	RLSE PER NPR 2451, WAS 87-5788-7-1	12/07/88
			A	REV PER ECN BD4493	12/17/88



1. RECEPTACLE ACCEPTS SIZE 20 PIN CONTACTS, CONTACTS MUST BE ORDERED SEPARATELY. ASSEMBLY MATES WITH ANY 25 POSN PLUG IN AMPLIMITE® SERIES.
2. NYLON, FLAME RETARDANT, UL 94V-0 RATEJ, GLASS FILLED, BLACK.
3. CARBON STEEL PER ASTM A 109.
4. TIN PLATING PER MIL-T-10727, COPPER PLATING PER MIL-C-14550, ZINC PLATING PER ASTM B633, TYPE III, CLASS SC1, CLEAR CHROMATE.
5. 5.08µm [1.000200] MIN TIN OVER 1.27µm [1.000050] MIN COPPER.
6. ZINC PLATED.
7. EACH PART INDIVIDUALLY BULK PACKED.



DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 [1.005] 3 PLC DEC ± 0.13 [1.005] ANGLES ± 2°		OR 06/07/89 L.SIPE CHK 6-28-89 M.G. LENKER APPD 6-25-89 R. WAYNE APPD 6-25-89 J. SHOMERS PRODUCT SPEC 108-40030 APPLICATION SPEC 114-40007 RETRY		AMP INCORPORATED Marsheburg, Pa. 17105	
MATERIAL INSERTS, △ SHELLS & SHIELDS, △ CLINCH NUTS, △		NAME RECEPTACLE KIT, UNASSEMBLED, WITH CLINCH NUTS, SIZE 3, 25 POSITION, SHIELDING HARDWARE, AMPLIMITE, HDP-20®		PART NO 749763-1	
FINISH SHELLS & SHIELDS, △ CLINCH NUTS, △		SIZE D CAGE CODE 00779 SCALE 4:1		DRAWING NO 749763 SHEET 1 OF 1	

CUSTOMER DRAWING