


REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APP
			H	REVISED PER EC 051A-0054-99	27AU699	JG

- 1
- UL RATED 94V-0 THERMOPLASTIC, BLACK.




2

3

4



TERMINATED VIEW



DETAIL Z
SCALE 10:1
TYPICAL

1.125	2.100	2.380	2.150	43	44	1-746285-3
1.625	3.100	3.380	3.150	63	64	1- -2
1.525	2.900	3.180	2.950	59	60	1- -1
1.275	2.400	2.680	2.450	49	50	1- -0
1.025	1.900	2.180	1.950	39	40	-9
.875	1.600	1.880	1.650	33	34	-8
.775	1.400	1.680	1.450	29	30	-7
.675	1.200	1.480	1.250	25	26	-6
.625	1.100	1.380	1.150	23	24	-5
.525	.900	1.180	.950	19	20	-4
.425	.700	.980	.750	15	16	-3
.375	.600	.880	.650	13	14	-2
.275	.400	.680	.450	9	10	746285-1
E	D	C	B	A	NO OF POSN	PART NUMBER

		E	D	C	B	A	NO OF POSN	PART NUMBER
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON : DECIMALS ± .005 ANGLES ± 5°		CONTRACT NO		AMP AMP INCORPORATED Harrisburg, Pa.				
		DR						
		J. PEACHEY 9-30-85		NAME RECEPTACLE KIT, AMP-LATCH NOVO, CTR & MIL PLZN, 15 GOLD DUPLEX CONTACTS, W/O STRAIN RLF				
		CHK 11-21-85						
W.E. ZELKO								
MATERIAL MOLDED PARTS:  CONTACTS: 		APPD 11-21-85		SIZE D FSCM NO 00779DRAWING NO 746285				
		APPD 11-21-85						
FINISH CONTACTS: 		D. HOFFMAN		SCALE 4 : 1				
		DSGN APPD						
		OTHER APPD		SHEET 1 of 1				