





ISS	ZONE	DESCRIPTION \ PER REQUEST \ DATE



RECOMMENDED
CABLE STRIPPING DIM'S



STAMP (IF ANY)

- 1. CRIMPED FERRULE
- 2. CRIMPED CONTACT PIN
- HEX CRIMP SIZE .068"

- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
- 1. BRASS PER QQ-B-626
- 2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
- 3. PHOSPHOR BRONZE PER QQ-B-750
- 4. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
- 5. PTFE MIL-P-1946B

DIMENSIONS ARE IN MILLIMETERS					PART NO.		TITLE	
UNLESS OTHERWISE SPECIFIED					B6121A1-NT3G-1-50		BNC CRIMP JACK	
TOLERANCES					APPROVED		DATE	
0.5-6 = ±0.2					CHECKED		DATE	
6-30 = ±0.4					DRAWN		DATE	
30-120 = ±0.6					SCALE		3/1	
120-315 = ±1					ISSUE		A	
315-1000 = ±1.6					FILE NO.			
1000-2000 = ±2.4					DRAWING NO.		KU-B6121A1-NT3G-58CU-50	
					ITEM NO.			

Amphenol

BNC CRIMP JACK

KU-B6121A1-NT3G-58CU-50

NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DRAWING NO.
1	HOUSING	NOTE 1	NOTE 2	1	B70000-1-46/31
2	BODY	NOTE 1	NOTE 2	1	B74000-2
3	INSULATOR	NOTE 5	NATURAL	1	B74000-3T-50
4	CONTACT PIN	NOTE 3	NOTE 4	1	B74000-8-25/11
5	FERRULE	COPPER	NOTE 2	1	FR-648/533X