



Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

4971NM

78621079753

Status:

Active

Description:

1/2 in. 90 degree nylon Ranger liquidtight cord connector, cord range .310-.560

Features

Extended range with superior strain relief.

Reduced overall size, fits into tighter spaces.

Gland nut designed to restrict cable bending.

Application

Provide a means for passing a cord cable into an enclosure through a bulkhead

Suitable for Ordinary, Wet or Dry locations.

General

Material

Nylon

Cord and Cable Types

S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

Dimension Information

Hub Size (inches)

3/4

Dimension A (inches)

1 13/32

Dimension B (inches)

1 3/8

Dimension C (inches)

5/8

Cord Range (inches)

.310-.560

Throat Diameter (inches)

0.79

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

10

Package in Units

50

T&B Sold in UOM

Each

T&B Weight Per UOM

10.8 lbs. per 100

Application Support

T&B Instruction Sheets

ta00927-tb2

Product Overview

Available on Website

Specifications

Available on Website

Portable Cord Selection Table

Available on Website

Certifications

RoHS Compliance

Yes

Certifications

File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com