



TOUCHPAD KEYBOARD

G80-11900



Available Part Numbers

G80-11900HRMUS Black, PS/2 Keyboard, PS/2 Touchpad Only

G80-11900HVMUS Black, PS/2 Keyboard, PS/2 Touchpad, AT & Serial Adapters Included

G80-11900LPMUS Beige, PS/2 Keyboard, PS/2 Touchpad Only

G80-11900LTMUS Beige, PS/2 Keyboard, PS/2 Touchpad, AT & Serial Adapters Included

Colors

Beige, Black

Dimensions

L x W x H = 16.3" x 7.6" x 1.45"

Keys

104 Key Windows Compatible

Laser Printed - Beige

Two Shot Molded - Black

Keyswitch Technology

MX Mechanical Keyswitch with Gold Crosspoint Contacts

Interfaces

Y Cable: PS/2 Keyboard, PS/2 Touchpad

Y Cable: PS/2 Keyboard w/ AT adapter, PS/2 Touchpad w/ Serial adapter

Integrated 2 Button Touchpad

X/Y Coordinate Resolution

500 dpi = 20 dots/mm

Optional Features

Multiple Languages Available

Power Supply

+5V/DC $\pm$ 5%, 35mA typical

Temperature

Storage Range: -4°F to +140°F

Operating Range: +32°F to +122°F

Reliability

MCBF: 1×10^9 cycles

MTBF: > 113,500 hours; Operating Life of Individual

Keys: > 50 million actuations



FCC Part 15 Subpart
B Class B

CISPR 22 EN 550 22

Cherry Electrical Products

Phone: 800 510 1689

Web: www.cherrycorp.com