




DIN 439 B

~ISO 4035

Standard withdrawn



BN 630

Hex jam nuts ~0,5d

Stainless steel A2

- ~UNI 5589
- ~ČSN 021403

[3D Cadenas](#)

M10; M12; M14: wrench size according to ISO on request

Article#	d ₁	e min.	s	m max.
3646069	M1,6	3,48	3,2	1
1241796	M2	4,32	4	1,2
1241818	M2,5	5,45	5	1,6
1241826	M3	6,01	5,5	1,8
1143700	(M3,5)	6,58	6	2
1241834	M4	7,66	7	2,2
1241842	M5	8,79	8	2,7
1241850	M6	11,05	10	3,2
1241869	M8	14,38	13	4
1241877	M10	18,9	17	5
1241885	M12	21,1	19	6
1397427	(M14)	24,49	22	7
1241893	M16	26,75	24	8
3092534	(M18)	29,56	27	9
1241907	M20	32,95	30	10
1210130	M24	39,55	36	12
1210149	(M27)	45,2	41	13,5
1210157	M30	50,85	46	15
1806629	(M33)	55,37	50	16,5
1806661	M36	60,79	55	18
1806696	M42	71,3	65	21