



Dimensions (In.)

Specifications:

- Impedance tolerance: $150\Omega \pm 25\%$ @ 100MHz
- DC resistance: $.50\Omega$ max.
- Rated current: 300mA max.
- Operating temperature: $-25^{\circ} \sim 85^{\circ}\text{C}$
- Storage temperature: $-40^{\circ} \sim 85^{\circ}\text{C}$

Ferrite Chip Beads provide an effective means of EMI/RFI attenuation for electronic equipment. These items are specially designed for flow, reflow, and wave soldering applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

436-1151