

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1201150055

Status:


Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change Molded Junction Box, Side Mount, Single Keyway with Mini-Change B-Size Molded Home Run Connector, 8 Ports, PNP, 0.30m Cable Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Passive Distribution Boxes
Series	120115
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
UPC	78678824068
Physical	
Bus I/O	Micro-Change (M12)
Cable Connector Orientation	Straight
Cable Length	N/A
Home Run Cable Length	0.305m
Home Run Connector	Micro-Change (M12) - 10 pole
Home Run Interface	Integrated Connector
Keyway	Single
LED Indicator	PNP Sensors
Material - Cable Jacket	PVC
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Orientation	Side Mount
Poles	5
Poles (wired)	4
Ports	8
Temperature Range - Operating	-20°C to +90°C
Wiring Configuration	Single I/O per Port
Electrical	
Current - Maximum per Contact	4.0A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC
Material Info	
Engineering Number	803P802
Reference - Drawing Numbers	
Sales Drawing	SD-120115-009

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120115 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION