





Copyright FCI.


C

D

- NOTES :
- 1- MATERIALS :  
BODY : High Temp thermoplastic 30% GF, COLOR BLACK UL94 V-0  
PIN : COPPER ALLOY
  - 2- 7N MIN PIN RETENTION IN EITHER DIRECTION
  - 3- RoHS COMPATIBLE PRODUCT SPECIFICATION :  
a- PLATING : LF means the product is Lead Free,  
2µ MIN matte Tin over 1.27µ Nickel underplating.  
b- MANUFACTURING PRODUCT SPECIFICATION :  
Housing will withstand exposure to 260°C peak temperature  
for 30 secondes in a convection infra-red or vapor phase oven.  
c- LABELLING :  
Meets packaging specs as per GS-14-920  
d- LEGAL STATMENT : See GS-47-0004
  - 4- PLANE REFERENCE -A- IS GENERATED BY LONG PINS TAIL ROW  
WITH LOWEST AREA OF BODY.  
SHORT PINS ROW TO BE FLUSH OR HIGHER 0.1 MAX ABOVE REF -A-.
  - 5- MINIMUM QUANTITY IN BLI BOX : 500




SCALE 3:1  
VIEW WITH  
PICK-UP CAP



|               |                                       |       |       |                                                                                       |                |            |
|---------------|---------------------------------------|-------|-------|---------------------------------------------------------------------------------------|----------------|------------|
| spec ref      | GS-12-652                             |       |       | dr                                                                                    | A Parrenin     | 2014/02/28 |
| tolerance std | TOLERANCES UNLESS OTHERWISE SPECIFIED |       |       | eng                                                                                   | A Parrenin     | 2014/03/19 |
| ISO 406       |                                       |       |       | chr                                                                                   | D Conveycey    | 2014/03/20 |
| ISO 1101      |                                       |       |       | appr                                                                                  | Gert Dreesbeke | 2014/03/21 |
| surface       | linear                                | 0.X   | ±0.30 |  |                |            |
|               |                                       | 0.XX  | ±0.13 |                                                                                       |                |            |
|               |                                       | 0.XXX | ±0.05 |                                                                                       |                |            |
| ISO 1302      | angular                               | 0°    | ±/°   | www.fci.com                                                                           | cat. no.       | -          |



www.fci.com

|          |                       |            |                        |                                                                                       |                                                                                       |              |                |           |
|----------|-----------------------|------------|------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------------|----------------|-----------|
|          | 2014/02/28            | projection | mm                     | size                                                                                  | A3                                                                                    | scale        | 4:1            |           |
|          | 2014/03/19            |            |                        |  |  | ecn no       | ELX-B-17245-1  |           |
|          | 2014/03/20            |            |                        |                                                                                       |                                                                                       |              |                |           |
| e        | 2014/03/21            |            |                        |                                                                                       |                                                                                       |              | product family | rel level |
| title    | HEADER UNSHROUDED SMT |            |                        | dwg no                                                                                | 10112690C                                                                             |              | rev            |           |
|          | DOUBLE ROW R/A        |            |                        |                                                                                       |                                                                                       |              |                | E         |
| cat. no. |                       | -          | Product - Customer Drw |                                                                                       |                                                                                       | sheet 1 of 1 |                |           |