


SEK 10P female connector

SEK 10P female connector



TOLERANCE FOR "L" LENGTH

| DIMENSION RANGE | TOLERANCE |
|-----------------|-----------|
| 0.0m - 1.0m     | +10/0 mm  |
| >1.0m - 3.0m    | +30/0 mm  |
| >3.0m - 5.0m    | +50/0 mm  |
| >5.0m - 10.0m   | +100/0 mm |
| >10.0m          | +200/0 mm |

NOTES:

- 1) CABLE MUST BE PERFORMED 100% CONTINUITY TEST.
- 2) WHITE LABEL CONTENT:

CMK/YR-XXXX-X-XX  
HARTING P/N

BLACK FONT, FONT HEIGHT: 3.5.

- 3) CABLE SHOULD BE FOLDED MANY CIRCLES ACCORDING TO TOTAL CABLE LENGTH AND PACKED BY A PLASTIC BAG (QTY ACCORDING TO ACTUAL CONDITION),STICK THE LABEL WITH P/N,QTY AND LOT NUMBER ON IT,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION).
- 4) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

|                                               |  |                        |  |
|-----------------------------------------------|--|------------------------|--|
| 33 18 243 100 0067                            |  | 1 m                    |  |
| 33 18 243 080 0066                            |  | 0.8 m                  |  |
| 33 18 243 050 0065                            |  | 0.5 m                  |  |
| 33 18 243 020 0064                            |  | 0.2 m                  |  |
| 33 18 243 010 0063                            |  | 0.1 m                  |  |
| Port-No.                                      |  | Dim.L                  |  |
|                                               |  | Tech Character.        |  |
| All dimensions in mm<br>Original Size DIM A 3 |  | Scale                  |  |
| Detail                                        |  | 03/07/08               |  |
| Drawn                                         |  | Aaron                  |  |
| Stand                                         |  | /                      |  |
| Mod                                           |  | Da.t.                  |  |
| Name                                          |  | ZHAHAI HARTING LIMITED |  |
| Sd                                            |  | TB 33 18 243 xxx 00xx  |  |
| Page                                          |  | /                      |  |