

Cable Ties

Cable Ties with Fasteners

Cable Tie Tools

Clamps and Clips

Mounts

Heavy Duty Mounts

Wiring Duct

Wiring Protection

Convoluted Tubing

Spiralwrap

Grommet

Electrical Tape

Labels, Printers and Software

Pre - Terminated Networking

Copper Network Solutions

Fiber Network Solutions

Jacks and Wall Plates

Residential Solutions

Racks - Cable Management

Surface Raceway Systems

1N0C

Spiralwrap .125" Diameter - Polyamide, Black, 100ft/reel

Article Number: 161 - 05002
Part Number: 1N0C
Type: 1N
Material: PA6



Find a Distributor


Order Samples

Get Technical Drawings

1. Base Data

Part No.	1N0C	
Type	1N	
Color	Black (BK)	
Features	Spiralwrap protective sheathing allows cables. The inner edges are beveled to Recognized Spiralwrap is reusable and Natural and black are standard colors (see may be available dependent upon volume HellermannTyton for more information.	flexible routing and lead - out of prevent damage to cables. U.L. resistant to most chemicals. material descriptions). Colors requirements. Contact
Application	- Control Cabinet Doors: Protects cable from friction when one end of the cable is fastened within the panel and the other is fastened to the panel door. Allows flexibility and prevents wire chafing when door is opened and closed. - Robotics: Protects hoses and wires during movement. - Pneumatic Hoses: Protects hoses from abrasion while on semi -trucks and other vehicles. - Spark Plug Wires: Lengthens the life of spark plug wires by reducing abrasion to wire insulation. Spiralwrap can be installed in two basic ways: - In a gapped installation, Spiralwrap is wrapped with space between the sheathing. This accommodates wire breakouts and also keeps the wire bundle flexible. - In a butted installation, Spiralwrap is wrapped so the sheathing completely insulates the wire bundle. This provides superior abrasion resistance and additional rigidity.	

2. Product Dimensions



Min. Ø Bundle	.0625 " / 1.60 mm
Max. Ø Bundle	.50 " / 12.7 mm
Ø D	.125 " / 3.18 mm
Wall Thickness (WT)	.015 "
Wall Thickness	.38 mm
Pitch	.187 " / 4.75 mm

4. Material and Specifications

Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL94 V2
Material Specification	RoHS
Operating Temperature	-121 °F to +212 °F (-85 °C to +100 °C)
ROHS Conformity	

Logistic and Packaging

Packaging Type	reel
Pkg. Qty.	100 ft / 30.48 m
Carton Qty.	100
UPC	08930600093

Miscellaneous

UL Recognized (US and Canada)	Yes	
Find a Distributor	Get Product Samples	Get Technical Drawings

Customers Who Bought This Item Also Bought

	Mark 7 - Tensioning and Cut -Off Tool for T18 -T50 and CTT20 -CTT60 Series Cable Ties Part No: MK7 Article No: 110 -07500
	Heavy Duty Mount, Mounting .25"" Max Torq 155 lb Max Dia for Washer .73"" Black, 100/pkg Part No: HDM250HIRC2 Article No: 151 -00437

This product was found in [Wiring Protection](#) > [Spiralwrap](#)