




MATERIALS:

Box and Cover: Glass filled nylon. Color: Blue

Marking: 4384

Screw: 4 Ea. Pan Head, self-tapping #2-32 cover crews. Carbon Steel.

Finish: Blue Zinc Plated

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

ORDERING INFORMATION: Model 4384-*

*=Color Code, -0 Black, -6 Blue

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA