

## Heavy-Duty Computer Power Extension Cord for Servers and Computers, 20A, 12AWG (IEC-320-C19 to IEC-320-C20) 10-ft.

MODEL NUMBER: **P036-010**



### Highlights

- C19 to C20 Power Cable, 10 ft.
- 12AWG x 3C, 20 Amp Rated
- RoHS Approved

### Package Includes

- C19 to C20 Power Cable, 10 ft.

### Description

Use Tripp Lite's P036-010 in server applications that require a higher rated, heavier gauge cable. C19 to C20 connectors, 3 x 12ga conductors, 20AMP rated, 250V - ideal for use with Blade Server Chassis.

### Features

- Molded, Heavy-Duty Power Cable, 10 ft.
- IEC-60320-C19 to IEC-60320-C20
- 12AWG x 3C, SJTW, 20A, 250Volt
- RoHS Approved

### Specifications

OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05

UPC ASSIGNMENT	
Unit Carton UPC#	037332176837
PHYSICAL	
Color	Black
Style	Power Cables
CONNECTIONS	
Connector A	IEC-320-C19
Connector B	IEC-320-C20
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

## Related Items

### Optional Products

Model Number	Description	Qty.
<a href="#">P036-002</a>	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20)	1
<a href="#">P036-002-19LA</a>	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 Left Angle to IEC-320-C20)	1
<a href="#">P036-002-19RA</a>	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 Right Angle to IEC-320-C20)	1
<a href="#">P036-002-20LA</a>	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20 Left Angle)	1
<a href="#">P036-002-20RA</a>	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20 Right Angle)	1
<a href="#">P036-006</a>	6-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20)	1
<a href="#">P036-006-2C19</a>	6-ft. AC Power Splitter Cable ( C20 to 2 x C19 )	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:  
<http://www.tripplite.com/sku/P036-010>.