



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		N1	REVISED PER ECO-09-024927	06NOV09	KK	AEG

D



C

B

A



- 1
- POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE OF BEAMS).
- 2
- TOLERANCE NON-CUMULATIVE.
- 3
- THE MATING END OF THE CONTACT IS IDENTIFIED BY THE LETTER "A" STAMPED ON THE RECEPTACLE BOX.
- 4
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE 4	3.120	2.964	20	2-87983-0
	2.964	2.808	19	1-87983-9
	2.808	2.652	18	1-87983-8
	2.652	2.496	17	1-87983-7
OBSOLETE 4	2.496	2.340	16	1-87983-6
	2.340	2.184	15	1-87983-5
	2.184	2.028	14	1-87983-4
	2.028	1.872	13	1-87983-3
	1.872	1.716	12	1-87983-2
	1.716	1.560	11	1-87983-1
	1.560	1.404	10	1-87983-0
4 OBSOLETE	1.404	1.248	9	87983-9
	1.248	1.092	8	87983-8
4 OBSOLETE	1.092	.936	7	87983-7
4 OBSOLETE	.936	.780	6	87983-6
	.780	.624	5	87983-5
OBSOLETE 4	.624	.468	4	87983-4
	.468	.312	3	87983-3
OBSOLETE 4	.312	.156	2	87983-2
	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± -		ASSY, MOD I, BOARD MOUNT RECP,			
		1 PLC ± -		.156CL , STD PRESSURE, TYPE A,			
		2 PLC ± -		FOR ROUND HOLE MOUNTING			
		3 PLC ± .005		SIZE			
MATERIAL: HOUSING-FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK		FINISH: .000079 MIN TIN		CAGE CODE			
CONTACTS: PHOS BRONZE				DRAWING NO			
				RESTRICTED TO			
				A2 00779 C=87983			
				SCALE 4:1 SHEET 1 OF 1 REV N1			
				CUSTOMER DRAWING			