

PRODUCT SPECIFICATION



Brand	C.K
Product Range	HDclassic Screwdrivers
Catalogue number	4810, 4811, 4812, 4813, 4814, 4815, 4816, 4965, 4975, 4977, 4987, 4334M, 4999
Date	19/04/2010

Range Description A range of professional quality engineers screwdrivers	
Features - Cellulose acetate handles – shatterproof and wipe clean - Non roll handle design – Specifically designed to stop the screwdrivers rolling off non flat surfaces - Toughened high alloy steel blades offering the ultimate in wear resistance and performance - Blade torque capacity up to 20% over the International standards requirement - Chrome plated shaft with black non peel tip finish for corrosion protection - Precision machined tips for the ultimate screw fit and high torque output	



4810



4811



4812



4813



4814



4815




4816



4965



4975



4977



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4810 03	HDclassic Screwdriver Slotted Flared Tip 5x75mm	5013969586503	82054000	6
T4810 03-H	HDclassic Screwdriver Slotted Flared Tip 5x75mm	5013969700398	82054000	6
T4810 04	HDclassic Screwdriver Slotted Flared Tip 6x100mm	5013969586602	82054000	6
T4810 04-H	HDclassic Screwdriver Slotted Flared Tip 6x100mm	5013969700404	82054000	6
T4810 05	HDclassic Screwdriver Slotted Flared Tip 7x125mm	5013969586701	82054000	6
T4810 05-H	HDclassic Screwdriver Slotted Flared Tip 7x125mm	5013969700411	82054000	6
T4810 06	HDclassic Screwdriver Slotted Flared Tip 8x150mm	5013969586800	82054000	6
T4810 06-H	HDclassic Screwdriver Slotted Flared Tip 8x150mm	5013969700428	82054000	6
T4810 08	HDclassic Screwdriver Slotted Flared Tip 9x200mm	5013969586909	82054000	6
T4810 08-H	HDclassic Screwdriver Slotted Flared Tip 9x200mm	5013969700435	82054000	6
T4810 10	HDclassic Screwdriver Slotted Flared Tip 10x250mm	5013969587005	82054000	6
T4810 10-H	HDclassic Screwdriver Slotted Flared Tip 10x250mm	5013969700442	82054000	6
T4810 12	HDclassic Screwdriver Slotted Flared Tip 12x250mm	5013969587104	82054000	6
T4810 12-H	HDclassic Screwdriver Slotted Flared Tip 12x250mm	5013969700459	82054000	6
T4811 04	HDclassic Screwdriver Slotted Strikethrough 6x100mm	5013969748802	82054000	6
T4811 04-H	HDclassic Screwdriver Slotted Strikethrough 6x100mm	5013969700466	82054000	6
T4811 06	HDclassic Screwdriver Slotted Strikethrough 8x150mm	5013969748901	82054000	6
T4811 06-H	HDclassic Screwdriver Slotted Strikethrough 8x150mm	5013969700473	82054000	6
T4811 08	HDclassic Screwdriver Slotted Strikethrough 10x200mm	5013969749007	82054000	6
T4811 08-H	HDclassic Screwdriver Slotted Strikethrough 10x200mm	5013969700480	82054000	6
T4811 10	HDclassic Screwdriver Slotted Strikethrough 13x250mm	5013969750003	82054000	6
T4811 10-H	HDclassic Screwdriver Slotted Strikethrough 13x250mm	5013969700497	82054000	6
T4812 0	HDclassic Screwdriver PH0x65mm	5013969587708	82054000	6

T4812 0-H	HDclassic Screwdriver PH0x65mm	5013969700671	82054000	6
T4812 1	HDclassic Screwdriver PH1x80mm	5013969587807	82054000	6
T4812 1-H	HDclassic Screwdriver PH1x80mm	5013969700688	82054000	6
T4812 2	HDclassic Screwdriver PH2x100mm	5013969587906	82054000	6
T4812 2-H	HDclassic Screwdriver PH2x100mm	5013969700695	82054000	6
T4812 3	HDclassic Screwdriver PH3x150mm	5013969588002	82054000	6
T4812 3-H	HDclassic Screwdriver PH3x150mm	5013969700701	82054000	6
T4812 4	HDclassic Screwdriver PH4x200mm	5013969588101	82054000	6
T4812 4-H	HDclassic Screwdriver PH4x200mm	5013969700718	82054000	6
T4813 0	HDclassic Screwdriver PZD0x60mm	5013969588507	82054000	6
T4813 0-H	HDclassic Screwdriver PZD0x60mm	5013969700596	82054000	6
T4813 1	HDclassic Screwdriver PZD1x80mm	5013969588606	82054000	6
T4813 1-H	HDclassic Screwdriver PZD1x80mm	5013969700602	82054000	6
T4813 2	HDclassic Screwdriver PZD2x100mm	5013969588705	82054000	6
T4813 2-H	HDclassic Screwdriver PZD2x100mm	5013969700619	82054000	6
T4813 3	HDclassic Screwdriver PZD3x150mm	5013969588804	82054000	6
T4813 3-H	HDclassic Screwdriver PZD3x150mm	5013969700626	82054000	6
T4813 4	HDclassic Screwdriver PZD4x200mm	5013969934908	82054000	6
T4813 4-H	HDclassic Screwdriver PZD4x200mm	5013969700633	82054000	6
T4814 25	HDclassic Screwdriver Stubby Slotted 6.5x25mm	5013969589009	82054000	6
T4814 25-H	HDclassic Screwdriver Stubby Slotted 6.5x25mm	5013969700336	82054000	6
T4814 31	HDclassic Screwdriver Stubby Slotted 8x25mm	5013969589108	82054000	6
T4814 31-H	HDclassic Screwdriver Stubby Slotted 8x25mm	5013969700343	82054000	6
T4815 1	HDclassic Screwdriver Stubby PH1x25mm	5013969589306	82054000	6
T4815 1-H	HDclassic Screwdriver Stubby PH1x25mm	5013969700374	82054000	6
T4815 2	HDclassic Screwdriver Stubby PH2x25mm	5013969589405	82054000	6
T4815 2-H	HDclassic Screwdriver Stubby PH2x25mm	5013969700381	82054000	6
T4816 1	HDclassic Screwdriver Stubby PZD1x25mm	5013969815900	82054000	6
T4816 1-H	HDclassic Screwdriver Stubby PZD1x25mm	5013969700350	82054000	6
T4816 2	HDclassic Screwdriver Stubby PZD2x25mm	5013969815801	82054000	6
T4816 2-H	HDclassic Screwdriver Stubby PZD2x25mm	5013969700367	82054000	6
T4965 03	HDclassic Screwdriver Slotted Parallel Tip 3x75mm	5013969605600	82054000	6
T4965 03-H	HDclassic Screwdriver Slotted Parallel Tip 3x75mm	5013969700503	82054000	6
T4965 04	HDclassic Screwdriver Slotted Parallel Tip 4x100mm	5013969605709	82054000	6
T4965 04-H	HDclassic Screwdriver Slotted Parallel Tip 4x100mm	5013969700510	82054000	6
T4965 05	HDclassic Screwdriver Slotted Parallel Tip 4.5x125mm	5013969605808	82054000	6
T4965 05-H	HDclassic Screwdriver Slotted Parallel Tip 4.5x125mm	5013969700527	82054000	6
T4965 06	HDclassic Screwdriver Slotted Parallel Tip 5x150mm	5013969605907	82054000	6
T4965 06-H	HDclassic Screwdriver Slotted Parallel Tip 5x150mm	5013969700534	82054000	6
T4965 08	HDclassic Screwdriver Slotted Parallel Tip 5x200mm	5013969606003	82054000	6

T4965 08-H	HDclassic Screwdriver Slotted Parallel Tip 5x200mm	5013969700541	82054000	6
T4965 12	HDclassic Screwdriver Slotted Parallel Tip 6x300mm	5013969606102	82054000	6
T4965 12-H	HDclassic Screwdriver Slotted Parallel Tip 6x300mm	5013969700558	82054000	6
T4975 06	HDclassic Screwdriver Long Reach Slotted Parallel Tip 3x150mm	5013969608403	82054000	6
T4975 06-H	HDclassic Screwdriver Long Reach Slotted Parallel Tip 3x150mm	5013969700565	82054000	6
T4975 08	HDclassic Screwdriver Long Reach Slotted Parallel Tip 3x200mm	5013969608502	82054000	6
T4975 08-H	HDclassic Screwdriver Long Reach Slotted Parallel Tip 3x200mm	5013969700572	82054000	6
T4975 10	HDclassic Screwdriver Long Reach Slotted Parallel Tip 4x250mm	5013969608601	82054000	6
T4975 10-H	HDclassic Screwdriver Long Reach Slotted Parallel Tip 4x250mm	5013969700589	82054000	6
T4977 1	HDclassic Screwdriver Long Reach PH1x250mm	5013969609202	82054000	6
T4977 1-H	HDclassic Screwdriver Long Reach PH1x250mm	5013969700749	82054000	6
T4977 2	HDclassic Screwdriver Long Reach PH2x250mm	5013969609301	82054000	6
T4977 2-H	HDclassic Screwdriver Long Reach PH2x250mm	5013969700756	82054000	6
T4987 1	HDclassic Screwdriver Long Reach PZD1x250mm	5013969816105	82054000	6
T4987 1-H	HDclassic Screwdriver Long Reach PZD1x250mm	5013969700640	82054000	6
T4987 2	HDclassic Screwdriver Long Reach PZD2x250mm	5013969816006	82054000	6
T4987 2-H	HDclassic Screwdriver Long Reach PZD2x250mm	5013969700657	82054000	6
T4999B	HDclassic Screwdriver Set	5013969294002	82054000	3
T4334M 03	HDclassic Nut Spinner 3mm	5013969533002	82054000	6
T4334M 035	HDclassic Nut Spinner 3.5mm	5013969533101	82054000	6
T4334M 04	HDclassic Nut Spinner 4mm	5013969533200	82054000	6
T4334M 045	HDclassic Nut Spinner 4.5mm	5013969533309	82054000	6
T4334M 05	HDclassic Nut Spinner 5mm	5013969533408	82054000	6
T4334M 055	HDclassic Nut Spinner 5.5mm	5013969533507	82054000	6
T4334M 06	HDclassic Nut Spinner 6mm	5013969533606	82054000	6
T4334M 07	HDclassic Nut Spinner 7mm	5013969533705	82054000	6
T4334M 08	HDclassic Nut Spinner 8mm	5013969533804	82054000	6
T4334M 09	HDclassic Nut Spinner 9mm	5013969533903	82054000	6
T4334M 10	HDclassic Nut Spinner 10mm	5013969534009	82054000	6
T4334M 11	HDclassic Nut Spinner 11mm	5013969534108	82054000	6
T4334M 12	HDclassic Nut Spinner 12mm	5013969534207	82054000	6
T4334M 13	HDclassic Nut Spinner 13mm	5013969534306	82054000	6

Technical product information	Blade/Shaft
-------------------------------	--------------------

	Made from chrome molybdenum vanadium steel, hardened to 57-59 HRC, Chrome plated with black non peel tip finish. Engineers screwdrivers slotted 5,5; 6,5; 8 and 10mm made from chrome vanadium steel, hardened to 53-55 HRC, black non peel finish. Handle The handle is Cellulose Acetate, injection moulded around the blade. The handles are shatterproof down to -35° C.
Standards compliance	Slotted screwdrivers DIN 5265, DIN 5263, DIN 5264A PZD/SDV Screwdrivers DIN 5262-B-PZ, DIN 5260-PZ, DIN/ISO 8764-1 & 2 PH Screwdrivers DIN 5262-B-PH, DIN 5260-PH, DIN/ISO 8764-1 & 2
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	HD Comfort Screwdrivers are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4810 03	24	24	165	57	-	-	-	-
T4810 03-H	24	24	16	57	49	27	215	65
T4810 04	27	27	200	70	-	-	-	-
T4810 04-H	27	27	200	70	49	30	250	78
T4810 05	27	27	225	125	-	-	-	-
T4810 05-H	27	27	225	125	49	30	275	133
T4810 06	29	29	260	159	-	-	-	-
T4810 06-H	29	29	260	159	49	32	310	167
T4810 08	33	33	320	180	-	-	-	-
T4810 08-H	33	33	320	180	49	36	370	188
T4810 10	33	33	380	281	-	-	-	-
T4810 10-H	33	33	380	281	59	36	430	290
T4810 12	33	33	430	349	-	-	-	-
T4810 12-H	33	33	430	349	59	36	480	358
T4811 04	27	27	200	159	-	-	-	-
T4811 04-H	27	27	200	159	49	30	250	167
T4811 06	29	29	260	180	-	-	-	-
T4811 06-H	29	29	260	180	49	32	310	188
T4811 08	33	33	320	273	-	-	-	-
T4811 08-H	33	33	320	273	35	36	370	280
T4811 10	33	33	380	413	-	-	-	-
T4811 10-H	33	33	380	413	5	36	430	423
T4812 0	19	19	130	27	-	-	-	-
T4812 0-H	19	19	130	27	49	22	180	35
T4812 1	24	24	170	57	-	-	-	-
T4812 1-H	24	24	170	57	49	27	220	65
T4812 2	27	27	200	88	-	-	-	-
T4812 2-H	27	27	200	88	49	30	250	96
T4812 3	28	28	260	157	-	-	-	-
T4812 3-H	28	28	260	157	49	31	310	165
T4812 4	33	33	320	188	-	-	-	-
T4812 4-H	33	33	320	188	59	36	370	195

T4813 0	19	19	130	27	-	-	-	-
T4813 0-H	19	19	130	27	49	22	180	36
T4813 1	24	24	170	57	-	-	-	-
T4813 1-H	24	24	170	57	49	27	220	65
T4813 2	27	27	200	70	-	-	-	-
T4813 2-H	27	27	200	70	49	30	250	78
T4813 3	29	29	260	135	-	-	-	-
T4813 3-H	29	29	260	135	49	32	310	143
T4813 4	33	33	320	57	-	-	-	-
T4813 4-H	33	33	320	57	35	36	370	64
T4814 25	31	31	85	56	-	-	-	-
T4814 25-H	31	31	85	56	49	34	135	64
T4814 31	31	31	85	57	-	-	-	-
T4814 31-H	31	31	85	57	49	34	135	65
T4815 1	31	31	85	52	-	-	-	-
T4815 1-H	31	31	85	52	49	34	135	60
T4815 2	31	31	85	56	-	-	-	-
T4815 2-H	31	31	85	56	49	34	135	64
T4816 1	31	31	85	52	-	-	-	-
T4816 1-H	31	31	85	52	49	34	135	60
T4816 2	31	31	85	56	-	-	-	-
T4816 2-H	31	31	85	56	49	34	135	64
T4965 03	19	19	145	26	-	-	-	-
T4965 03-H	19	19	145	26	49	22	195	34
T4965 04	22	22	180	43	-	-	-	-
T4965 04-H	22	22	180	43	49	25	230	51
T4965 05	22	22	205	50	-	-	-	-
T4965 05-H	22	22	205	50	49	25	255	58
T4965 06	24	24	240	57	-	-	-	-
T4965 06-H	24	24	240	57	49	27	290	66
T4965 08	24	24	290	68	-	-	-	-
T4965 08-H	24	24	290	68	49	27	340	76
T4965 12	27	27	400	131	-	-	-	-
T4965 12-H	27	27	400	131	49	30	450	139
T4975 06	22	22	230	40	-	-	-	-
T4975 06-H	22	22	230	40	49	25	280	48
T4975 08	22	22	280	43	-	-	-	-

T4975 08-H	22	22	280	43	49	25	330	51
T4975 10	22	22	330	50	-	-	-	-
T4975 10-H	22	22	330	50	49	25	380	58
T4977 1	27	27	350	100	-	-	-	-
T4977 1-H	27	27	350	100	49	30	400	108
T4977 2	29	29	360	145	-	-	-	-
T4977 2-H	29	29	360	145	49	32	410	153
T4987 1	27	27	350	100	-	-	-	-
T4987 1-H	27	27	350	100	49	30	400	108
T4987 2	29	29	360	110	-	-	-	-
T4987 2-H	29	29	360	110	49	32	410	118
T4999B	180	50	380	1110	180	50	380	1110
T4334M 03	24	24	215	74	45	27	265	82
T4334M 035	24	24	215	74	45	27	265	82
T4334M 04	24	24	215	74	45	27	265	82
T4334M 045	24	24	215	75	45	27	265	82
T4334M 05	24	24	215	77	45	27	265	85
T4334M 055	24	24	215	78	45	27	265	85
T4334M 06	24	24	215	78	45	27	265	85
T4334M 07	27	27	225	113	45	30	275	121
T4334M 08	27	27	225	115	45	30	275	122
T4334M 09	27	27	225	116	45	30	275	123
T4334M 10	27	27	225	118	45	30	275	125
T4334M 11	29	29	235	139	45	32	285	146
T4334M 12	29	29	235	165	45	32	285	172
T4334M 13	29	29	235	168	45	32	285	175

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4810 03	80	168	35	389		
T4810 03-H	95	270	55	459		
T4810 04	100	203	35	474		
T4810 04-H	95	270	55	537		
T4810 05	110	230	40	830		
T4810 05-H	95	330	60	887		

T4810 06	110	263	40	1034		
T4810 06-H	100	360	65	1117		
T4810 08	105	323	60	1192		
T4810 08-H	110	450	70	1280		
T4810 10	105	383	60	1798		
T4810 10-H	95	560	75	1897		
T4810 12	110	433	40	2199		
T4810 12-H	95	560	75	2304		
T4811 04	100	203	35	1008		
T4811 04-H	95	270	55	1070		
T4811 06	110	263	40	1161		
T4811 06-H	100	360	65	1244		
T4811 08	100	323	40	1719		
T4811 08-H	100	360	65	1796		
T4811 10	105	383	60	2596		
T4811 10-H	95	560	75	2694		
T4812 0	80	160	35	209		
T4812 0-H	85	230	50	266		
T4812 1	100	173	35	396		
T4812 1-H	95	270	55	459		
T4812 2	100	203	35	582		
T4812 2-H	95	270	55	645		
T4812 3	110	263	40,0	1023		
T4812 3-H	90	260	55	1056		
T4812 4	110	323	40	1209		
T4812 4-H	100	360	65	1286		
T4813 0	60	160	35	207		
T4813 0-H	85	230	50	272		
T4813 1	80	173	35	389		
T4813 1-H	95	270	55	459		
T4813 2	110	230	40	501		
T4813 2-H	95	270	55	537		
T4813 3	110	263	40	891		
T4813 3-H	100	360	65	974		
T4813 4	105	323	60	454		
T4813 4-H	100	360	65	500		
T4814 25	80	200	50	385		

T4814 25-H	95	270	55	453		
T4814 31	80	200	50	391		
T4814 31-H	95	270	55	459		
T4815 1	80	200	50	360		
T4815 1-H	95	270	55	429		
T4815 2	80	200	50	384		
T4815 2-H	95	270	55	453		
T4816 1	80	200	50	360		
T4816 1-H	95	270	55	429		
T4816 2	80	200	50	384		
T4816 2-H	95	270	55	453		
T4965 03	60	160	35	195		
T4965 03-H	85	230	50	260		
T4965 04	80	183	35	305		
T4965 04-H	95	270	55	375		
T4965 05	80	203	35	347		
T4965 05-H	95	270	55	417		
T4965 06	90	243	40	415		
T4965 06-H	95	330	60	486		
T4965 08	90	293	40	475		
T4965 08-H	100	360	65	572		
T4965 12	110	403	40	892		
T4965 12-H	95	560	75	991		
T4975 06	100	360	65	356		
T4975 06-H	100	360	65	404		
T4975 08	100	360	65	374		
T4975 08-H	100	360	65	422		
T4975 10	110	450	70	453		
T4975 10-H	110	450	70	501		
T4977 1	90	353	40	667		
T4977 1-H	110	450	70	800		
T4977 2	110	363	40	975		
T4977 2-H	110	450	70	1071		
T4987 1	110	353	40	705		
T4987 1-H	110	353	40	753		
T4987 2	110	363	40	765		
T4987 2-H	110	363	40	813		

T4999B	200	370	160	3570		
T4334M 03	95	330	60	582		
T4334M 035	110	230	40	573		
T4334M 04	95	330	60	582		
T4334M 045	95	270	55	560		
T4334M 05	95	270	55	578		
T4334M 055	95	270	55	578		
T4334M 06	95	330	60	600		
T4334M 07	95	330	60	816		
T4334M 08	95	330	60	822		
T4334M 09	95	330	60	828		
T4334M 10	95	330	60	840		
T4334M 11	95	330	60	966		
T4334M 12	95	330	60	1122		
T4334M 13	95	330	60	1140		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4810 03	-	-	-	-	-	-	47	Box
T4810 03-H	7,6	Hanger	-	-	-	-	69	Box
T4810 04	-	-	-	-	-	-	54	Box
T4810 04-H	7,6	Hanger	-	-	-	-	69	Box
T4810 05	-	-	-	-	-	-	80	Box
T4810 05-H	7,6	Hanger	-	-	-	-	89	Box
T4810 06	-	-	-	-	-	-	80	Box
T4810 06-H	7,6	Hanger	-	-	-	-	115	Box
T4810 08	-	-	-	-	-	-	112	Box
T4810 08-H	7,6	Hanger	-	-	-	-	152	Box
T4810 10	-	-	-	-	-	-	112	Box
T4810 10-H	9,0	Hanger	-	-	-	-	157	Box
T4810 12	-	-	-	-	-	-	105	Box
T4810 12-H	9,0	Hanger	-	-	-	-	156	Box
T4811 04	-	-	-	-	-	-	54	Box
T4811 04-H	7,6	Hanger	-	-	-	-	68	Box
T4811 06	-	-	-	-	-	-	81	Box

T4811 06-H	7,6	Hanger	-	-	-	-	116	Box
T4811 08	-	-	-	-	-	-	81	Box
T4811 08-H	6,5	Hanger	-	-	-	-	116	Box
T4811 10	-	-	-	-	-	-	112	Box
T4811 10-H	9,0	Hanger	-	-	-	-	156	Box
T4812 0	-	-	-	-	-	-	47	Box
T4812 0-H	7,6	Hanger	-	-	-	-	56	Box
T4812 1	-	-	-	-	-	-	54	Box
T4812 1-H	7,6	Hanger	-	-	-	-	69	Box
T4812 2	-	-	-	-	-	-	54	Box
T4812 2-H	7,6	Hanger	-	-	-	-	69	Box
T4812 3	-	-	-	-	-	-	81	Box
T4812 3-H	7,6	Hanger	-	-	-	-	66	Box
T4812 4	-	-	-	-	-	-	81	Box
T4812 4-H	6,5	Hanger	-	-	-	-	116	Box
T4813 0	-	-	-	-	-	-	39	Box
T4813 0-H	7,6	Hanger	-	-	-	-	56	Box
T4813 1	-	-	-	-	-	-	47	Box
T4813 1-H	7,6	Hanger	-	-	-	-	69	Box
T4813 2	-	-	-	-	-	-	81	Box
T4813 2-H	7,6	Hanger	-	-	-	-	69	Box
T4813 3	-	-	-	-	-	-	81	Box
T4813 3-H	7,6	Hanger	-	-	-	-	116	Box
T4813 4	-	-	-	-	-	-	112	Box
T4813 4-H	6,5	Hanger	-	-	-	-	116	Box
T4814 25	-	-	-	-	-	-	49	Box
T4814 25-H	7,6	Hanger	-	-	-	-	69	Box
T4814 31	-	-	-	-	-	-	49	Box
T4814 31-H	7,6	Hanger	-	-	-	-	69	Box
T4815 1	-	-	-	-	-	-	48	Box
T4815 1-H	7,6	Hanger	-	-	-	-	69	Box
T4815 2	-	-	-	-	-	-	48	Box
T4815 2-H	7,6	Hanger	-	-	-	-	69	Box
T4816 1	-	-	-	-	-	-	48	Box
T4816 1-H	7,6	Hanger	-	-	-	-	69	Box
T4816 2	-	-	-	-	-	-	48	Box
T4816 2-H	7,6	Hanger	-	-	-	-	69	Box

T4965 03	-	-	-	-	-	-	39	Box
T4965 03-H	7,6	Hanger	-	-	-	-	56	Box
T4965 04	-	-	-	-	-	-	47	Box
T4965 04-H	7,6	Hanger	-	-	-	-	69	Box
T4965 05	-	-	-	-	-	-	47	Box
T4965 05-H	7,6	Hanger	-	-	-	-	69	Box
T4965 06	-	-	-	-	-	-	67	Box
T4965 06-H	7,6	Hanger	-	-	-	-	90	Box
T4965 08	-	-	-	-	-	-	67	Box
T4965 08-H	7,6	Hanger	-	-	-	-	116	Box
T4965 12	-	-	-	-	-	-	106	Box
T4965 12-H	7,6	Hanger	-	-	-	-	157	Box
T4975 06	-	-	-	-	-	-	116	Box
T4975 06-H	7,6	Hanger	-	-	-	-	116	Box
T4975 08	-	-	-	-	-	-	116	Box
T4975 08-H	7,6	Hanger	-	-	-	-	116	Box
T4975 10	-	-	-	-	-	-	153	Box
T4975 10-H	7,6	Hanger	-	-	-	-	153	Box
T4977 1	-	-	-	-	-	-	67	Box
T4977 1-H	7,6	Hanger	-	-	-	-	152	Box
T4977 2	-	-	-	-	-	-	105	Box
T4977 2-H	7,6	Hanger	-	-	-	-	153	Box
T4987 1	-	-	-	-	-	-	105	Box
T4987 1-H	7,6	Hanger	-	-	-	-	105	Box
T4987 2	-	-	-	-	-	-	105	Box
T4987 2-H	7,6	Hanger	-	-	-	-	105	Box
T4999B		-	-	-	-	-	234	Box
T4334M 03	6,6	Hanger	-	-	-	-	90	Box
T4334M 035	6,6	Hanger	-	-	-	-	81	Box
T4334M 04	6,6	Hanger	-	-	-	-	90	Box
T4334M 045	6,6	Hanger	-	-	-	-	68	Box
T4334M 05	6,6	Hanger	-	-	-	-	68	Box
T4334M 055	6,6	Hanger	-	-	-	-	68	Box
T4334M 06	6,6	Hanger	-	-	-	-	90	Box
T4334M 07	6,6	Hanger	-	-	-	-	90	Box
T4334M 08	6,6	Hanger	-	-	-	-	90	Box
T4334M 09	6,6	Hanger	-	-	-	-	90	Box

T4334M 10	6,6	Hanger	-	-	-	-	90	Box
T4334M 11	6,6	Hanger	-	-	-	-	90	Box
T4334M 12	6,6	Hanger	-	-	-	-	90	Box
T4334M 13	6,6	Hanger	-	-	-	-	90	Box