


03 Combination Pliers

DIN ISO 5746


- ▶ with gripping zones for flat and round material, suitable for versatile use
- ▶ with cutting edges for soft and hard wire
- ▶ long cutting edges for thicker cables
- ▶ cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- ▶ special tool steel, oil-hardened and tempered



Gripping zone for flat material



Gripping zone for round material



Cutting edges for wire and cable

03 01 180



03 02 180



03 05 180



03 06 180



Article-No.	EAN-Code	Head	Handles	Cutting capacities				g
				●	●	●		
Length mm	Code 4003773-			ø mm	ø mm	ø mm	mm ²	
03 00	180 015161	polished	black afromentized	3.4	2.2	12.0	16.0	210
	200 015178			3.8	2.5	13.0	16.0	260
	250 015185			3.8	2.5	15.0	25.0	440
03 01	140 015192	polished	plastic coated	2.8	1.8	9.0	10.0	110
	160 013235			3.1	2.0	10.0	16.0	180
	180 013242			3.4	2.2	12.0	16.0	220
	200 013259			3.8	2.5	13.0	16.0	280
	250 015222			3.8	2.5	15.0	25.0	480
03 02	160 023203	polished	with two-colour dual component handles	3.1	2.0	10.0	16.0	215
	180 023197			3.4	2.2	12.0	16.0	260
	200 034940			3.8	2.5	13.0	16.0	330
03 05	140 039730	chrome plated	with two-colour dual component handles	2.8	1.8	9.0	10.0	135
	160 039518			3.1	2.0	10.0	16.0	215
	180 034933			3.4	2.2	12.0	16.0	260
	200 041146			3.8	2.5	13.0	16.0	330
03 06	160 021902	chrome plated	insulated with two-colour dual component handles	3.1	2.0	10.0	16.0	220
	180 021926			3.4	2.2	12.0	16.0	265
	200 033776			3.8	2.5	13.0	16.0	335
03 07	160 015307	chrome plated	plastic dipped insulated	3.1	2.0	10.0	16.0	265
	180 015314			3.4	2.2	12.0	16.0	305
	200 015321			3.8	2.5	13.0	16.0	380
	250 015345			3.8	2.5	15.0	25.0	610