


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DESCRIPTION	CABLE DIAMETER	PACKAGING	APPROXIMATE WEIGHT (CABLE ONLY)	JACKET TYPE
PUP5504**-UY	CATEGORY 5e UTP 4-PAIR 24AWG	0.1931IN(4.90MM) NOMINAL	1000 FT [305 M] IN AN EASY PAYOUT BOX	21 LB/1000 FT [9.5 Kg/305M]	CMP
PUR5504**-UY	CATEGORY 5e UTP 4-PAIR 24AWG	0.2251IN(5.71MM) NOMINAL	1000 FT [305 M] IN AN EASY PAYOUT BOX	22 LB/1000 FT [10.0 Kg/305M]	CMR


A



NOTES:

B

- ** - INDICATES JACKET COLOR
SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE JACKET COLOR.
- DIMENSIONS IN BRACKETS ARE METRIC.
- COLOR CODE: PAIR 1 WHITE/BLUE - BLUE
PAIR 2 WHITE/ORANGE - ORANGE
PAIR 3 WHITE/GREEN - GREEN
PAIR 4 WHITE/BROWN - BROWN

MODEL FILENAME M01948CY_PUP5504UY_00.PRT		SIZE A
DRAWING FILENAME M01948CY_DC65/00B		
TX5500 CATEGORY 5E UTP CABLE CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		I.I. NUMBER
		PRODUCT SPEC/ PKG SPEC
 ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°		ASSY METHOD/ TEST METHOD
DRAWN BY BJN		SCALE NONE
DATE 12-18-07		PART NO. SEE TABLE
CHK'D GEF		DRAWING NO. 01948-65

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	9-25-08	BJN	GEF	B. WEIGHT WAS 25LB(11.3KG) A. CABLE DIAMETER NOW NOMINAL	01948-65		GAZ		
R	12-18-07	BJN	GEF	RELEASED TO PRODUCTION	01948-65		GAZ		