

Product Reference

[Chevin Contract](#)


General Information

High quality surface mounted luminaire complete with 65° - 200 cd/m² (Cat 2) louvre or prismatic panel, suitable for a multitude of internal applications.

- **F Marked.**
- **Complete with 3500°K Halophosphate lamps.**
- **Slim body.**
- **High quality aluminium louvre or TP(b) rated prismatic panel.**
- **Lift and tilt attachment installation.**
- **Matching emergency version available.**



Chevin Contract



Specification

Brand:	Crompton
No. of Lamps:	Single or twin
Lamp Wattage (W):	36, 58 or 70
Lamp Length/Type:	T8 Fluorescent - Halophosphate
Circuit Type:	Switch Start or High Frequency
Dimensions - Length (mm):	1250 (36w), 1550 (58w), 1814 (70w)
Width (mm):	225
Depth (mm):	82
IP Rating:	IP20
Cable Entry:	Rear
Emergency Conversion:	Integral
Duration:	3 hour

Catalogue numbers

	Switch start	High frequency	Switch start emergency	High frequency emergency
65° (Cat 2) Louvre				
1x36w	CHC136S	CHC136Z	EBCHC136S	EBCHC136Z
2x36w	CHC236S	CHC236Z	EBCHC236S	EBCHC236Z
1x58w	CHC158S	CHC158Z	EBCHC158S	EBCHC158Z
2x58w	CHC258S	CHC258Z	EBCHC258S	EBCHC258Z
1x70w	CHC170S	CHC170Z	EBCHC170S	EBCHC170Z
2x70w	CHC270S	CHC270Z	EBCHC270S	EBCHC270Z
Prismatic Panel				
1x58w	-	CHCP158Z	-	EBCHCP158Z
2x58w	-	CHCP258Z	-	EBCHCP258Z
1x70w	-	CHCP170Z	-	EBCHCP170Z
2x70w	-	CHCP270Z	-	EBCHCP270Z