

MICRO SWITCH



A DIVISION OF MINNEAPOLIS HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929

ASSEMBLY-
TOGGLE SWITCH

CATALOG LISTING



22AT21-T



N.C. TO C. CIRCUIT MADE (ALL SWITCHES) (MAINTAINED POSITION).

N.O. TO C. CIRCUIT MADE (SWITCHES 5,6,7, AND 8)

N.C. TO C. CIRCUIT MADE (SWITCHES 1,2,3, AND 4) (MOMENTARY POSITION).



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

ELECTRICAL DATA

CONTACT ARRANGEMENT

(8) S.P.D.T.

250 VAC ————— 5 AMP

30 VOLTS DC RATING

INDUCTIVE ——— SEA LEVEL ——— 3 AMP
50,000 FT. ——— 2.5 AMPRESISTIVE ——— SEA LEVEL ——— 5 AMP
50,000 FT. ——— 5 AMP

MAXIMUM INRUSH ——— 24 AMP

SCALE— FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ± 1°

WEIGHT

NOTE—

- ⑧
1—UNIT INCLUDES (8) CAT. LIST. ISM3-T BASIC SWITCH.
2—SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY.
3—TERMINALS ARE PLATED FOR SOLDERING.
4—UNIT WILL PERFORM SATISFACTORILY IN TEMPERATURES
FROM 250°F TO MINUS 65°F.