

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301070042](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Watertite Wet Location 26W Fluorescent Stringlight 12/3 SOOW 10 Lamps Lead, 35.05m (115.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130107
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Overview	Stringlights
Product Name	Watertite
Type	String Lights
UPC	78678834335

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	59.70m (2.350")
Duty	Wet Location
Guard Included	No
Guard Type	Steel
Height	445.01mm (17.520")
Length	35.05m (115.0')
Material - Globe	Butyrate
Material - Guard	N/A
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Rubber Molded

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	12/3 SOOW
Lamp Type	PL-C 26/41/4P
Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	387010A
--------------------	---------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130107](#) Series