


Dimensions: mm (in)

**Electrical Specifications:**

- Contact Resistance: 20mΩ max. Initial @ 2-4 VDC 100mA
- Insulation Strength: 1000MΩ min
- Dielectric Strength: 1000 V RMS@sea level
- Rating: 1A / 250VAC, 3A / 120VAC or 28 VDC

Mechanical Specifications:

- Mechanical Life: 50,000 make-and break cycles
- Operating Temperature: -30°C to +85°C

Soldering Process:

- Manual Soldering: Use soldering iron of 30 watts, controlled at 350°C approximately 5 sec. while applying solder.
- Wave Soldering: Recommended Soldering Temperature: 260±5°C
Duration of Solder Immersion: 5±1sec. (PCB is 1.6mm in thickness)

Note:

- RoHS Compliant by Exemption

Sealed Sub-Miniature Toggle Switch
108-2AS3T1205-EVX

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2AS3T1205-EVX](#)