



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ sockets ▶ sockets ▶ MBI 1

MBI 1

datasheet for MBI 1
article number: 930308104



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 930 308-104
description:	2 mm diameter miniature socket, insulated, tin-plated copper beryllium contact (spring-loaded), with solder connection. Suitable for installation in equipment chassis and switch panels up to a maximum wall thickness of 5 mm.
typ:	MBI 1 gruen/green
system:	2mm system
order number:	930 308-104
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	2 mm socket (spring-loaded)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	6 A
Please consider derating curve!	
contact resistance:	10 mOhm
mounting:	screw
material	
contact material:	contact spring: copper - beryllium
contact surface material:	tin
housing material:	PA
connecting nut material:	brass nickel - plated
environmental conditions:	
temperature range:	-20 °C to +60 °C
drawing	
	