









Copyright FCI

PRODUCT NUMBER  
SEE TABLE



mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family LATCH-N-LOK				
ltr	ecn no	dr	date	tolerances unless otherwise specified						title				
B	V51458	MSC	11/27/95	angles <div>linear</div>		.XX±.01/XX±.03		INCH/MM 		LNL FEMALE HEADER, ASS'Y 2X10 ( CLINCHER TERMINAL )				
C	V80772	LSS	5/16/95			.XXX±.005/XX±.13								
D	V12179	TFG	6/24/01			.XXX±.0020/XXX±0.05								
E	M05-0062	MHT	4/4/05	dr	D. WHITING	10/15/90	scale 1:1 		dwg no sheet 1 of 2 size 79459 A3					
F	M05-0243	MHT	11/22/05	engr	D. HORCHLER	10/15/90								
G	M06-0285	AGS	7/28/06	chr	D. HORCHLER	10/15/90								
H	M09-0048	MHT	3/12/09	appd	D. HORCHLER	10/15/90								
sheet	revision	H	H											
index	sheet	1	2											

PRODUCT NUMBER	COLOR	REMARKS	LEAD FREE OPTION
79459-X01	70343 LIGHT GRAY	N/A	
-X02	80166 OFF WHITE		
-X03	70634 DARK GRAY		
-X04	701 BLACK		
-X05	70511 SLATE GRAY		
-X07	70455 SILVER GRAY	N/A	
-193	DARK GRAY	NOTE 4	
79459-199	PEBBLE GRAY	NOTE 4	


OBSOLETE

NOTES 5,6

OBSOLETE

# NOTES:

- HEADER MAT'L: G. F. POLYESTER 94V-0 RATED
- GROUND CONTACT MAT'L: 3/4 HARD PHOS BRONZE  
PLATED 200u"/5.08u 93/7 TIN LEAD.  
LEAD FREE OPTION:  
PLATED 200u"/5.08u PURE TIN.
- SIGNAL CONTACT MAT'L: BERYLLIUM-COPPER ALLOY  
PLATED 30u"/.76u PALLADIUM ALLOY WITH GOLD  
FLASH OVER 50u"/1.27u NICKEL
- TO BE PRINTED IN LOCATION SHOWN WITH: 79459-199  
1252-2681  
WK/YR
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER  
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.



## RECOMMENDED PCB LAYOUT

mat'l. code	surface ISO 1902	tolerance ISO 406 ISO 1101	projection	product family
ltr	ecp no	dr	date	title
H				LNL FEMALE HEADER, ASS'Y
				2X10 ( CLINCHER TERMINAL )
				dwg no
				79459
				type
				Product Customer Drawing
sheet	revision			
index	sheet			