



|              |                 |
|--------------|-----------------|
| <b>Wheel</b> | R-Rubber wheel  |
|              | C-Casting wheel |
|              | N-Nylon wheel   |

| Model No.      | Allowable Load (kg) | Net Weight(g) | Code No. |
|----------------|---------------------|---------------|----------|
| No.420-G-N25-1 | 10                  | 30            | 9713     |
| No.420-G-N32-2 | 18                  | 40            | 9714     |
| No.420-G-N38-3 | 28                  | 70            | 9715     |
| No.420-G-N50-4 | 38                  | 150           | 9716     |
| No.420-G-N65-5 | 55                  | 250           | 9717     |
| No.420-G-N75-6 | 65                  | 330           | 9718     |

| No. | D    | E  | F<br>(Turning<br>Radius) | G     | H  | J    | L1 | L2 | P1 | P2 | W               |                  |                |
|-----|------|----|--------------------------|-------|----|------|----|----|----|----|-----------------|------------------|----------------|
|     |      |    |                          |       |    |      |    |    |    |    | Rubber<br>Wheel | Casting<br>Wheel | Nylon<br>Wheel |
| 1   | φ 25 | 9  | R23                      | φ 4.2 | 35 | t1.4 | 30 | 35 | 23 | 28 | 12              | 12               | 12             |
| 2   | φ 32 | 11 | R28                      |       | 42 |      | 32 | 38 | 24 | 30 | 14              | 14               | 14             |
| 3   | φ 38 | 13 | R32                      | φ 5.3 | 50 | t1.6 | 38 | 46 | 28 | 36 | 17              | 17               | 16             |
| 4   | φ 50 | 16 | R42                      | φ 6.5 | 65 | t1.8 | 47 | 59 | 35 | 46 | 20              | 21               | 21             |
| 5   | φ 65 | 21 | R55                      | φ 8.8 | 80 | t2.3 | 58 | 70 | 42 | 55 | 26              | 25               | 25             |
| 6   | φ 75 |    | R60                      |       | 90 |      |    |    |    |    |                 |                  |                |