



PART NUMBERS	MATERIAL	LEGENDS	"A" +/- .062	"B" +/- .062	MARKERS PER CARDS	STD. PKG. QTY.	STD. CTN. CARDS	STYLE
PPM-0 THRU PPM-25	TEDLAR	'0' THRU '25'	.250 (6.35)	1.50 (38.1)	36	25 CARDS	100	A
PPM-1-33	TEDLAR	'1' THRU '33'	.273 (6.93)	1.50 (38.1)	33	25 CARDS	100	B
PPM-A THRU PPM-C	TEDLAR	'A' THRU 'Z'	.250 (6.35)	1.50 (38.1)	36	25 CARDS	100	A

NOTES:
1. MILLIMETER ARE IN ().

STYLE A
PPM-7



STYLE A
PPM-1-33



										CAD FILENAME/LAYERS				100295CD_DC_C10050/04A								
										PANDUIT CORP. TINLEY PARK, ILLINOIS												
										PRE-PRINTED MARKER CARDS PPM TYPE CUSTOMER DRAWING												
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.								
										DRAWN BY RVU		MAT'L: SEE TABLE.				SCALE NTS						
0	9/1/09	RVU		DRAWING RELEASE.			5820	R			DATE 09/01/09					DRAWING NO. C10050				DWG A SIZE		
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP					CHK'D						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PPM-6](#) [PPM-1](#) [PPM-0](#) [PPM-10](#) [PPM-3](#) [PPM-16](#) [PPM-9](#) [PPM-19](#) [PPM-15](#) [PPM-8](#) [PPM-23](#) [PPM-2](#) [PPM-25](#)
[PPM-7](#) [PPM-4](#) [PPM-5](#) [PPM-24](#) [PPM-11](#) [PPM-13](#) [PPM-18](#) [PPM-17](#) [PPM-1-33](#) [PPM-C](#) [PPM-A](#) [PPM-12](#) [PPM-20](#)
[PPM-B](#) [PPM-14](#)