



T-6 T-Stripper Wire Stripper

Catalog # 45-121



Features

- Wire range #14 to #24 AWG solid, #16 to #26 AWG stranded
- Form-ground, hardened, knife-type blades for accurate stripping
- Tough steel construction
- Built-in wire cutter and wire looping holes
- Plier nose for extra gripping strength
- Laser-etched wire gauge markings
- Spring-loaded automatic opening
- Corrosion-resistant, black oxide finish

Engineered to strip every wire right



Kinetic™ Reflex™ T®-Stripper Wire Stripper

Ergonomic handles with Santoprene™ grip and Thumb Valley™ make this the premier wire stripper in the market.



Kinetic™ Super Wire Stripper

The ergonomic design and patented Santoprene™ grip wicks away perspiration and reduces muscle fatigue. The Thumb Valley™ guide and precision stripping holes promote the highest accuracy in the industry.



Reflex™ Super T®-Stripper Wire Stripper

The ergonomic design with curved handles reduces wrist fatigue. Features 6/32 and 8/32 self-chasing, bolt cutting holes and a locking pawl for safe storage.



Reflex™ Premium T®-Stripper Wire Stripper

Designed for total-comfort and wire stripping. Ergonomic handles fit an electrician's natural grip and reduces hand fatigue. Textured, slip-resistant sleeves cushion thumb and fingers.

- Locking Pawl
- Bolt Cutting
- Extended Textured Comfort
- Ergo Handles

Super T®-Stripper Wire Stripper

Traditional T®-Stripper Wire Stripper features with the added convenience of bolt-cutting holes and locking pawl. Curved comfort-grip handles accommodate high-volume wire stripping.



- Extended Textured
- Ergo Handles

T®-Stripper Wire Stripper

The industry standard for almost 50 years. Compact, lightweight and easy to use. Features precision-ground, knife-type blades, built-in looping holes, wire cutters and a convenient plier nose.

- Straight Handles



- Locking Pawl
- Bolt Cutting
- Comfort
- Curved Handles

T®-Stripper Wire Stripper Selection Guide

6	8	10	12	14	16	18	20	22	24	26	28	30	Hole Size		#45-100's	#45-300's	#45-400's	#45-600's	#45-700's	#45-900's
8	10	12	14	16	18	20	22	24	26	28	30	32								
								22	24	26	28	30	Solid		45-125	45-317	45-417	—	—	—
								24	26	28	30	32	Stranded							
				14	16	18	20	22	24				Solid		45-121	45-316	45-416	45-616	45-716	—
				16	18	20	22	24	26				Stranded							
		10	12	14	16	18							Solid		45-120	—	45-415	—	45-715	45-915
		12	14	16	18	20							Stranded							
	8	10	12	14	16								Solid		—	45-315	—	45-615	—	—
	10	12	14	16	18								Stranded							
6	8	10	12	14									Solid		45-124	45-318	45-418	45-618	45-718	45-918
8	10	12	14	16									Stranded							
													T-Cutter		45-123	—	—	—	—	—

Static Disp

T®-Stripper Wire Strippers

- Form-ground, knife-type blades for accurate, easy stripping without nicking insulation
- Built-in wire cutter and looping holes
- Convenient plier nose for extra gripping strength
- Laser-etched wire gauge for easy-to-read visibility
- Spring-loaded automatic opening
- Corrosion-resistant, black oxide finish
- Tough steel construction



Description	Solid	Stranded	Cat. No.
T®-5 T®-Stripper Wire Stripper	10-18	12-20	45-120
T®-6 T®-Stripper Wire Stripper	14-24	16-26	45-121
T®-7 T®-Stripper Wire Stripper	22-30	24-32	45-125
T®-8 T®-Stripper Wire Stripper	6-14	8-16	45-124
T®-Stripper Wire Stripper – Metric	0.75-6mm ²		45-120-341
T®-Stripper Wire Stripper – Metric	0.5-4mm ²		45-125-341

NM Cable T®-Stripper Wire Strippers

- Easy, one-step stripping of outer jacket of NM cable – no slitting required
- Versatility to strip, cut and loop conductor wires with precision and ease
- Stripping holes for 12 or 14 AWG solid wire
- Locking pawl for safe storage



Description	Cat. No.
14/2 NM Cable T®-Stripper Wire Stripper	45-248
12/2 NM Cable T®-Stripper Wire Stripper	45-249
Reflex™ Super 12/2 & 14/2 NM Cable T®-Stripper Wire Stripper	45-621
Reflex™ Super 12/3 & 14/3 Cable T®-Stripper Wire Stripper	45-622

NM Cable Dual-Hole T®-Stripper Wire Stripper

- Stripping holes for stripping two 12 AWG or two 14 AWG wires simultaneously
- Ability to strip both conductor wires of NM cable at one time



Description	Wire Range	Cat. No.
Premium T®-14 T®-Stripper Wire Stripper	12 or 14 AWG solid	45-247

Romex® is a registered trademark of Southwire.

Super T®-Stripper Wire Strippers

- 6-32 and 8-32 self-chasing screw-cutting holes (not available on metric stripper)
- Curved, cushion-grip handles for ergonomic comfort
- Locking pawl to keep stripper in closed position
- Built-in wire cutter and looping holes
- Convenient plier nose for extra gripping strength
- Laser-etched wire gauge for easy-to-read visibility
- Spring-loaded automatic opening
- Tough steel construction, corrosion-resistant, black oxide finish



Description	Solid	Stranded	Cat. No.
Super T®-5 T®-Stripper Wire Stripper	8-16	10-18	45-315
Super T®-8 T®-Stripper Wire Stripper	6-14	8-16	45-318
Super T®-Stripper Wire Stripper – Metric	0.5-4mm ²		45-310-341
Super T®-Stripper Wire Stripper – Metric	0.75-6mm ²		45-315-341
Super T®-Stripper Wire Stripper – Metric	0.5-4mm ²		45-317-341

Lil' Ripper Stripper™


- Rips Romex® outer jacket cleanly and quickly
- Clips outer sheathing to remove excess Romex® jacket
- Strips inner conduit wires
- Looping holes loop wire for screw-on connections
- Twist-Assist™ tightens most popular sizes of winged twist-on connectors
- Injection molded elastomer grip provides a comfortable, slip resistant grip
- Strip length measuring scale allows for quick and easy measurements
- Conveniently fits in your pocket



Description	Cat. No.
Lil' Ripper Stripper™	45-025

Reflex™ Super T®-Stripper Wire Strippers

- 6/32 and 8/32 self-chasing screw-cutting holes
- Locking pawl for safe storage
- Ergonomic design for maximum comfort
- Curved handles reduce wrist fatigue
- Sleeves that extend to stripping head to cushion thumb and fingers
- Textured sleeves with extra cushioning for added comfort



Description	Solid	Stranded	Cat. No.
Reflex™ Super 12/2 & 14/2 NM Cable T®-Stripper Wire Stripper	12-2 and 14-2	—	45-621
Reflex™ Super 12/3 & 14/3 NM Cable T®-Stripper Wire Stripper	12-3 and 14-3	—	45-622