

Marker sheet - PKE 9X20 - 0803980

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Marker sheet, Sheet, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Insert, Cable diameter: >10 mm, Lettering field: 9 x 20 mm



The illustration shows versions PKT and PKE

Key commercial data

Packing unit	1 PCE
Minimum order quantity	12 PCE
Weight per Piece (excluding packing)	22.86 GRM
Custom tariff number	39269097
Country of origin	Italy

Technical data

Dimensions

Width (a)	9 mm
-----------	------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-50 °C ... 120 °C

General

Note	Can be labeled with CMS
Color	white
Components	Halogen-free
Inflammability class according to UL 94	V0
Material	ABS-PC
Number of individual labels	20
Number of individual labels per row	4

Marker sheet - PKE 9X20 - 0803980

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27149103
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410