

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.





All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
55308-XXX

PLATING OPTION
3= 0.76 µm GOLD
5= 1.27 µm GOLD


HOLD DOWN OPTION
1= OUTSIDE
2= INSIDE

TERMINAL LOADING
1 = FULLY LOADED 6 POS
2 = ONLY POS 2.3.4.5 LOADED
3 = ONLY POS 1.2.5.6 LOADED






RECOMMENDED PIPET
SCALE 2

INSIDE VERSION




OUTSIDE VERSION




REFERENCE PLAN
DEFINED BY THE
BEARING SURFACE

NOTES:

- 1 - MATERIAL: HOUSING: HIGH TEMP. PLASTIC, COLOR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE
SOLDER TAIL: 90/10 SnPb 2 µm MIN.
NO RAW EDGES EXCEPT SOLDER TAIL TIPS.
- 3 - PACKAGING IN TAPE & REEL SEE TA858.
- 4 - DIMENSION MEASURED FROM "B" TO THE TOP OF PRODUCT
- 5 - RECOMMENDED VACCUM PIPET

 www.fciconnect.com			surface 		tolerance ±0.13 ±2 °	projection 	mm 	
Dr	D LEGRAND	02.05.23	Product family MODULAR JACK			size	Scale	
Eng	F TISSERAND	02.05.23	Spec ref			A3	5:2	
Chr	F TISSERAND	02.05.23	Material SEE NOTES			ECN	F20562	
Appr	F TISSERAND	02.05.23						
title	HORIZONTAL L.P. SMT				dwg no	55308		Rev. F
	6 POSITIONS							
catalog no				SEE TABLE		CUSTOMER COPY		sheet 1 of 2

ltr	ecn no	dr	date
D	F20300	DLE	02.04.23
E	F20520	DLE	02.09.06
F	F20562	BLE	02.10.16
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-




Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

RECOMMENDED PCB FOOT PRINT
FOR 6 POSITIONS OUTSIDE



RECOMMENDED PCB FOOT PRINT
FOR 6 POSITIONS INSIDE



RECOMMENDED PANEL CUTOUT

FCI www.fciconnect.com				surface - ☒ ISO 1302	tolerance ±0.13 ±2 °	projection	mm
Dr	D LEGRAND	02.05.23	Product family	MODULAR JACK	size	A3	Scale 5:1
Eng	F TISSERAND	02.05.23	Spec ref		ECN	F20562	
Chr	F TISSERAND	02.05.23	Material	SEE NOTES			
Appr	F TISSERAND	02.05.23					
title	HORIZONTAL L.P. SMT				dwg no	55308	Rev. F
	6 POSITIONS						
catalog no	SEE TABLE				CUSTOMER COPY	sheet 2 of 2	