

SERIES 48EM:



Actual Size



FLEX-TECH MINIATURE SEALED PUSHBUTTON SWITCHES

This rugged multi-option sealed pushbutton series offers the utmost in choices of mounting styles, colors, terminations, bezels, lighting and momentary or alternate-action switching. The Series 48 offers all these options in one compact package size.

KEY FEATURES:

- Momentary or maintained action
- Gold contacts
- Many button colors
- Choice of LED colors
(or non-lighted versions)
- Long life
- Solder or PC terminals
- Panel sealed to IP 67

ORDERING INFORMATION:

Switch Function	Switch Termination	Module Type	Bezel Type	LED Color	Button Color	Mounting Type	Voltage Resistor
Momentary	Solder Tabs	48-1	RB - Round, Black	N - None	RD - Red	B - Bushing	If Blank*
Maintained	Solder Tabs	48-2	SB - Square, Black	R - Red	GR - Green	S - Snap-fit	05 - 5V forward
Momentary	PC	48-5	RC - Round, Chrome	G - Green	BK - Black		
Maintained	PC	48-6	SC - Square, Chrome	Y - Yellow	BL - Blue		
Momentary	Wire Leads	48-A		A - Amber	YL - Yellow		
Maintained	Wire Leads	48-B		B - Blue	OR - Orange		
				W - White	CR - Chrome		
					PK - Black with Standby Symbol		

APPLICATIONS


- Office equipment
- Medical equipment
- Industrial machinery
- Outdoor controls
- Mass transportation
- Food processing equipment

STANDARDS / AGENCY / RATINGS:

* Current limiting resistor is required to limit LED forward current to 20 mA (not included).



PRODUCT DRAWINGS



MECHANICAL / ELECTRICAL CHARACTERISTICS:

Circuit:

SPST-NO-DB

Button travel (nominal):

0.09 inches / 2.3 mm

Operating force (nominal):

3N / 306 grams

Contact bounce (nominal):

1 millisecond

Panel thickness:

0.02 – 0.12 inches / 0.5 – 3mm

Temperature index:

-40° F to +185° F

LED operating temperature:

-13° F to +185° F /

-25° C to +85° C

Current ratings (resistive):

250mA @ 12VDC, 100K cycles

150mA @ 28VDC, 150K cycles
(momentary)

100mA @ 48VDC, 100K cycles

10mA @ 12VDC, 1 million cycles
(momentary)

Dielectric strength:

1,000 VAC

Insulation resistance:

1G OHM

Contact resistance:

50 mΩ max (initial)

Torque (max):

10 inch pounds

Kit Contents		
Description	Quantity	Comments
Switches	8	
Actuators		
Round	14	2 each of the following colours: Blue, Red, Yellow, Orange, Green, Black, Chrome
Round with Hole	14	2 each of the following colours: Blue, Red, Yellow, Orange, Green, Black, Chrome
Square	14	2 each of the following colours: Blue, Red, Yellow, Orange, Green, Black, Chrome
Square with Hole	14	2 each of the following colours: Blue, Red, Yellow, Orange, Green, Black, Chrome
Rubber Washers	8	
Nuts	8	
LEDs	6	
Round Bezels	8	4x Black, 4x Chrome
Square Bezels	8	4x Black, 4x Chrome
Tweezers	1 Pair	