


# LOW PROFILE DUAL WIPE SOCKET

(1.27 mm) .050" PITCH • CLP SERIES



**CLP**  
**Mates:**  
FTSH, FTS, FW

| CLP | 1 | NO. PINS PER ROW | 02 | PLATING OPTION | ROW OPTION | OTHER OPTIONS |
|-----|---|------------------|----|----------------|------------|---------------|
|-----|---|------------------|----|----------------|------------|---------------|

## SPECIFICATIONS

**Insulator Material:**  
Black Liquid Crystal Polymer  
**Contact Material:**  
Phosphor Bronze  
**Plating:**  
Sn or Au over  
50 μ" (1.27 μm) Ni  
**Operating Temp Range:**  
-55 °C to +125 °C  
**Current Rating (CLP/FTSH):**  
3.4 A per pin  
(2 pins powered)  
**Voltage Rating:**  
280 VAC/396 VDC  
**Insertion Depth:**  
Top Entry =  
(1.40 mm) .055" minimum  
Bottom Entry =  
(2.41 mm) .095" minimum  
plus board thickness  
DH Entry =  
(2.31 mm) .091" to (2.67 mm) .105"  
**Max Cycles:**  
100 with 10 μ" (0.25 μm) Au

## PROCESSING

**Lead-Free Solderable:**  
Yes  
**SMT Lead Coplanarity:**  
(0.10 mm) .004" max (02-35)  
(0.15 mm) .006" max (36-50)\*  
\*(.004" stencil solution  
may be available; contact  
ipg@samtec.com)

02 thru 50

**-F**  
= Gold flash  
on contact,  
Matte Tin  
on tail

**-L**  
= 10 μ"  
(0.25 μm)  
Gold on  
contact,  
Matte Tin  
on tail

**-G**  
= 10 μ"  
(0.25 μm)  
Gold  
(-D only)

**-D**  
= Double  
Row

**-DH**  
= Double  
Horizontal  
(Requires  
FTSH-04  
lead style)

**-BE**  
= Bottom Entry  
(Required for bottom  
entry applications)

**-A**  
= Alignment Pin  
(Not available with -PA option)  
(05, 06, 07, 08, 10, 12, 15,  
20, 25, 30, 40 positions only)  
(-DH option and other sizes.  
Contact Samtec.)


**-K**  
= (4.00 mm) .157" DIA  
Polyimide film Pick & Place Pad

**-P**  
= Pick & Place Pad  
(5 positions min. -D only)  
(Not always necessary  
for auto placement.  
See Flex Processing.)

**-PA**  
= Pick & Place Pad  
with Alignment Pin  
(-D only)  
(Not available with -A option)

**-TR**  
= Tape & Reel


**-FR**  
= Full Reel Tape & Reel  
(must order maximum  
quantity per reel;  
contact Samtec for  
quantity breaks)



## ALSO AVAILABLE

Contact Samtec


Single row  
Other platings




**Notes:**  
Severe Environment  
Testing qualified; aligns  
with MIL-DTL-55302.  
Visit [samtec.com/set](http://samtec.com/set)

Some lengths, styles and  
options are non-standard,  
non-returnable.

| PIN/ROW | A           |
|---------|-------------|
| 04-15   | (3.56) .140 |
| 16-50   | (7.11) .280 |



If odd pins/row, alignment pins are on  
middle position on centerline of the part.  
If even pins/row, then alignment pins are  
between middle two positions.



-PA OPTION



-P OPTION