


(2,00 mm) .0787"

**BTMM SERIES**

# LOW PROFILE SQUARE POST JUMPER

## SPECIFICATIONS

For complete specifications see [www.samtec.com?BTMM](http://www.samtec.com?BTMM)

**Insulator Material:**  
Black Liquid Crystal Polymer

**Terminal Material:**  
Phosphor Bronze

**Plating:**  
Sn over 50 $\mu$ " (1,27 $\mu$ m) Ni

**Operating Temp Range:**  
-55°C to +105°C

**RoHS Compliant:**  
Yes

**Lead-Free Solderable:**  
Yes

## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



Choice of Single or Double row



Up to 50 pins per row

(0,50 mm)  
.020"  
square

(2,00 mm)  
.0787"  
pitch

(8,00 mm)  
.315" pitch

(4,00 mm)  
.157" pitch



**Note:** Some sizes, styles and options are non-standard, non-returnable.