

SPECIFICATIONS


(RoHS Compliant)

Model Number: SD12B1
Part Number: 19028933A

Drawing Number: 26021556A00
Date: Jan.01.2013



Mechanical Drawing:



Motor:

Nominal Voltage	= 12 vdc
Operating Voltage Range	= 6 – 14 vdc
Nominal Running Current	= 0.250 amps
Locked Rotor Current	= 1.20 amps
Running Power	= 3.0 watts
Average Speed	= 3500
Bearings	= Ball
Air Flow	= 35 CFM
Acoustic	= 47.6 dBA

Construction:

Venturi: Single Piece Die-Cast Zinc Alloy, Black
 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 83,000 hours at 40°C.

Additional Features:

Brushless DC Motor	
Polarity Protected	
Electronic Locked Rotor Protection	
Automatic Restart Capability	
Operating Temperature:	-10°C to 70°C
Storage Temperature:	-40°C to 85°C

Termination:

12" Lead wires, AWG 22, UL 1061

Red = Power (+)
 Black = Return (-)

Agency Approvals:

UL, CE