


[Request more info](#)
**Part Number : 5700100293F**


5700100293F

- 5700100XXXXF IGS
- 5700100XXXXF STP



This is a  
RoHS Compliant Product  
[To learn more click here](#)

### General Description

Series	570
Configuration	2 mm Lens
Description	2 mm Tri-Level CBI G-B-Y
Package Options	Bulk Packaging
Sizes	2mm
Lamp Type	Tri-Level Housing
Viewing	Right Angle
Polarity	Cathode Left
Lens Style	Tinted, Diffused
Viewing Angle	70
LED Centerline	1.78mm

### Absolute Maximum Ratings (Ta = 25°)

Solder Temperature	260 for 5 secs
Operating Temperature	-40 to +85
Storage Temperature	-40 to +85

### Operating Characteristics

Peak Wave Length	565	468	590
LED Position	1	2	3
Luminous Intensity Min	5	380	5
Luminous Intensity Typical	10	600	8
Forward Voltage Typical	2.2	3.5	2.1
Forward Voltage Max	2.5	4	2.5
Test Current mA	10mA		
Pitch Between Vertical	3.30		
Power Dissipation Max	105mW	105mW	105mW