



Wiha TORX® SoftFinish® Screwdrivers - Ergonomic Cushion Grip Handle



SHOP

362 TORX® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item No. | Size | mm | Inch | mm | Inch | mm | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 362 64 | T5 | 60 | 2.4 | 2.5 | .098 | 164 | 6.5 | .05 | 10 |
| 362 66 | T6 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 68 | T7 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 70 | T8 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 72 | T9 | 60 | 2.4 | 4.0 | .157 | 171 | 6.7 | .10 | 10 |
| 362 74 | T10 | 80 | 3.1 | 4.0 | .157 | 191 | 7.5 | .11 | 10 |
| 362 76 | T15 | 80 | 3.1 | 4.0 | .157 | 191 | 7.5 | .11 | 10 |
| 362 78 | T20 | 100 | 3.9 | 4.0 | .157 | 211 | 8.3 | .11 | 10 |
| 362 80 | T25 | 100 | 3.9 | 4.5 | .177 | 211 | 8.3 | .12 | 10 |
| 362 82 | T27 | 115 | 4.5 | 5.5 | .216 | 233 | 9.2 | .19 | 10 |
| 362 84 | T30 | 115 | 4.5 | 6.0 | .236 | 233 | 9.2 | .20 | 10 |
| 362 86 | T40 | 130 | 5.1 | 7.0 | .275 | 254 | 10.0 | .27 | 10 |
| 362 88 | T45 | 130 | 5.1 | 8.0 | .315 | 254 | 10.0 | .31 | 10 |



SHOP



SHOP

362 91 Set 6 Pcs. TORX®

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item No. | Size | mm | Size | mm | lbs. | | |
|----------|--------|----|------|--------|------|----|-----|
| 362 91 | 362 66 | T6 | 60 | 362 72 | T9 | 60 | .77 |
| | 362 68 | T7 | 60 | 362 74 | T10 | 80 | |
| | 362 70 | T8 | 60 | 362 76 | T15 | 80 | |

362 01 Set 6 Pcs. TORX®

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item No. | Size | mm | Size | mm | lbs. | | |
|----------|--------|-----|------|--------|------|-----|-----|
| 362 01 | 362 66 | T6 | 60 | 362 76 | T15 | 80 | .83 |
| | 362 70 | T8 | 60 | 362 78 | T20 | 100 | |
| | 362 74 | T10 | 80 | 362 80 | T25 | 100 | |

362 94 Set 8 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item No. | Size | mm | Size | mm | lbs. | | |
|----------|--------|-----|------|--------|------|-----|------|
| 362 94 | 362 66 | T6 | 60 | 362 78 | T20 | 100 | 1.24 |
| | 362 70 | T8 | 60 | 362 80 | T25 | 100 | |
| | 362 74 | T10 | 80 | 362 82 | T27 | 115 | |
| | 362 76 | T15 | 80 | 362 84 | T30 | 115 | |



SHOP

362 67 Set 12 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item No. | Size | mm | Size | mm | lbs. | | |
|----------|--------|-----|------|--------|------|-----|------|
| 362 67 | 362 64 | T5 | 60 | 362 76 | T15 | 80 | 2.03 |
| | 362 66 | T6 | 60 | 362 78 | T20 | 100 | |
| | 362 68 | T7 | 60 | 362 80 | T25 | 100 | |
| | 362 70 | T8 | 60 | 362 82 | T27 | 115 | |
| | 362 72 | T9 | 60 | 362 84 | T30 | 115 | |
| | 362 74 | T10 | 80 | 362 86 | T40 | 130 | |



Wiha Tamper Resistant TORX® Drivers



SHOP

362 TR Tamper Resistant TORX® Screwdriver With Wiha-SoftFinish® Handle. Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item | Size | mm | Inch | mm | Inch | mm | Inch | lbs. | pkg. |
|--------|------|-----|------|-----|------|-----|------|------|------|
| 362 69 | T7s | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 71 | T8s | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 73 | T9s | 60 | 2.4 | 4.0 | .157 | 171 | 6.7 | .10 | 10 |
| 362 75 | T10s | 80 | 3.1 | 4.0 | .157 | 191 | 7.5 | .11 | 10 |
| 362 77 | T15s | 80 | 3.1 | 4.0 | .157 | 191 | 7.5 | .11 | 10 |
| 362 79 | T20s | 100 | 3.9 | 4.0 | .157 | 211 | 8.3 | .11 | 10 |
| 362 81 | T25s | 100 | 3.9 | 4.5 | .177 | 211 | 8.3 | .11 | 10 |
| 362 83 | T27s | 115 | 4.5 | 5.5 | .216 | 233 | 9.2 | .19 | 10 |
| 362 85 | T30s | 115 | 4.5 | 6.0 | .236 | 233 | 9.2 | .20 | 10 |
| 362 87 | T40s | 130 | 5.1 | 7.0 | .275 | 254 | 10.0 | .28 | 10 |



SHOP

362 98 Set 7 Pcs. Tamper Resistant TORX®

| Item | Size | mm | Size | mm | lbs. | | |
|--------|--------|------|------|--------|------|-----|-----|
| 362 98 | 362 69 | T7s | 60 | 362 77 | T15s | 80 | .95 |
| | 362 71 | T8s | 60 | 362 79 | T20s | 100 | |
| | 362 73 | T9s | 60 | 362 81 | T25s | 100 | |
| | 362 75 | T10s | 80 | | | | |



SHOP

362 59 Set 10 Pcs. Tamper Resistant TORX®

| Item | Size | mm | Size | mm | lbs. | | |
|--------|--------|------|------|--------|------|-----|-----|
| 362 59 | 362 69 | T7s | 60 | 362 79 | T20s | 100 | 1.5 |
| | 362 71 | T8s | 60 | 362 81 | T25s | 100 | |
| | 362 73 | T9s | 60 | 362 83 | T27s | 115 | |
| | 362 75 | T10s | 80 | 362 85 | T30s | 115 | |
| | 362 77 | T15s | 80 | 362 87 | T40s | 130 | |

Wiha SoftFinish® ESD Safe Handle



SHOP

ESD Safe (10⁶-10⁹ Ohm)

362 ESD Safe TORX® Screwdriver, With Wiha-SoftFinish® Handle
DIN EN 61340-5-1/ 61340-5-2 Round blade, CVM steel, hardened, hard chromed. Offers protection against electrostatic discharge. Dissipative SoftFinish® cushion grip handle, multi-component.

| Item | Size | mm | Inch | mm | Inch | mm | Inch | lbs. | pkg. |
|--------|------|-----|------|-----|------|-----|------|------|------|
| 362 60 | T3 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 04 | T4 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 00 | T5 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 06 | T6 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 08 | T8 | 60 | 2.4 | 3.5 | .139 | 164 | 6.5 | .06 | 10 |
| 362 09 | T9 | 60 | 2.4 | 4.0 | .157 | 171 | 6.7 | .10 | 10 |
| 362 18 | T10 | 80 | 3.1 | 4.0 | .157 | 191 | 7.5 | .11 | 10 |
| 362 19 | T15 | 80 | 3.1 | 4.0 | .157 | 191 | 7.5 | .11 | 10 |
| 362 24 | T20 | 100 | 3.9 | 4.0 | .157 | 211 | 8.3 | .11 | 10 |



SHOP

362 89 Set 6 Pcs. ESD Safe TORX® Screwdrivers

| Item | Size | mm | Size | mm | lbs. | | |
|--------|--------|----|------|--------|------|-----|-----|
| 362 89 | 362 06 | T6 | 60 | 362 18 | T10 | 80 | .81 |
| | 362 08 | T8 | 60 | 362 19 | T15 | 80 | |
| | 362 09 | T9 | 60 | 362 24 | T20 | 100 | |

See SoftFinish® Cushion Grip Screwdrivers On Pages 65-70

See ESD Safe Pliers/Cutters & Precision Drivers On Pages 71, 127-132