

Part Number: SMT-1141-T-3-R



Features

Mounting: Surface Mount
Frequency: 4100 +/- 500 Hz
This part is RoHS 2002/95/EC Compliant.


Electrical Specifications

Operating Voltage	1-25 Vp-p
Rated Current (Max.)	2.9 mA
Rated Voltage	5 Vp-p
Resonant Frequency	41 +/- 500 Hz
Sound Pressure Level @ 10 cm (Min.)	73 dBA

Case Material: Liquid Crystal Polymer
Weight: 0.3g
Pin Material: Tin Plated Phosphor Bronze
Environmentally friendly.


Mechanical

Dimensions are in millimeters, tolerance is ± 0.5 unless otherwise specified.



Performance

Typical SPL vs. Frequency



For application notes and detail drawing specifications, please consult www.projectsunlimited.com.

Specifications subject to change without notice.

© 2005, Projects Unlimited Inc., All Rights Reserved.