

Standard Keyboard

G81-3000



Facts & Features

- FTSC Technology (mechanical individual keys with membrane contact switches)
- Robust and reliable
- High-quality keyboard for professional users
- Timeless design
- Also available without "Windows® keys" (101/102 keys)
- Operating life of individual keys > 50 million operations
- PC- and MAC- compatible due to USB interface

Delivery volume

- 1 standard keyboard
- 1 printed manual

Approvals

- FCC, cURus, GS, CE, c-tick, GOST-R
- Windows™ 2000, XP, Vista

System requirements

- PS/2 interface (PS/2 version)
- USB interface (USB version)

Technical data

- Number of buttons:
101 = european layout without Windows™ keys
102 = international layout without Windows™ keys
104 = european layout with Windows™ keys
105 = international layout with Windows™ keys
- Weight:
approx. 1400 g (without packaging)
approx. 1620 g (with packaging)
- Dimensions in mm:
approx. 470 x 195 x 44 (keyboard)
approx. 500 x 255 x 50 (packaging)
- Cable length:
approx. 1.75 m
- Storage temperature:
-20 °C until 60 °C
- Operating temperature:
0 °C until 50 °C
- Operating life of individual keys:
> 50 million operations
- Reliability:
MCBF > 10⁹ operations
MTBF > 80 000 hours
- Interface:
PS/2 (PS/2 version)
USB (USB version)
- Current consumption:
approx. 35 mA
- Packaging unit:
45 keyboards per master carton
2 master cartons per pallet
- Gurantee period:
2 years

Order description

<i>Order number</i>	<i>Housing colour</i>	<i>Number of buttons</i>	<i>Interface</i>	<i>Country version</i>	<i>EAN-Code</i>
G81-3000LPDDE-0	light grey	102	PS/2	Germany	4025112026003
G81-3000LPDES-0	light grey	102	PS/2	Spain	4025112046667
G81-3000LPDFR-0	light grey	102	PS/2	France	4025112046650
G81-3000LPDGB-0	light grey	102	PS/2	UK-English	4025112046643
G81-3000LPDIT-0	light grey	102	PS/2	Italy	4025112046636
G81-3000LPDRA-0	light grey	102	PS/2	UK-English / Cyrillic	4025112024917
G81-3000LPDUS-0	light grey	101	PS/2	US-English	4025112046629
G81-3000LPNBE-0	light grey	104	PS/2	Belgium	4025112010057
G81-3000LPNCD-0	light grey	105	PS/2	Canada	4025112017414
G81-3000LPNES-0	light grey	105	PS/2	Spain	4025112010125
G81-3000LPNGB-0	light grey	105	PS/2	UK-English	4025112010095
G81-3000LPNIT-0	light grey	105	PS/2	Italy	4025112036507
G81-3000LPNNO-0	light grey	105	PS/2	Norway	4025112026409
G81-3000LPNPO-0	light grey	105	PS/2	Portugal	4025112040375
G81-3000LPNRD-0	light grey	105	PS/2	Germany / Cyrillic	4025112032332
G81-3000LPNTS-0	light grey	105	PS/2	Czech Republic	4025112040016
G81-3000LRNBB-0	light grey	104	PS/2	Bulgaria	4025112010088
G81-3000LRNBE-0	light grey	105	PS/2	Belgium	4025112044359
G81-3000LRNCH-0	light grey	105	PS/2	Switzerland	4025112051289
G81-3000LRNCH-2	black	105	PS/2	Switzerland	4025112044366
G81-3000LRNDE-0	light grey	105	PS/2	Germany	4025112002250
G81-3000LRNDE-2	black	105	PS/2	Germany	4025112044373
G81-3000LRNDK-0	light grey	105	PS/2	Denmark	4025112051784
G81-3000LRNDK-2	black	105	PS/2	Dänemark	4025112044380
G81-3000LRNES-2	black	105	PS/2	Spain	4025112044397
G81-3000LRNEU-0	light grey	104	PS/2	US-English / € - Symbol	4025112053771
G81-3000LRNEU-2	black	104	PS/2	US-English / € - Symbol	4025112044458
G81-3000LRNFR-0	light grey	105	PS/2	France	4025112053788

<i>Order number</i>	<i>Housing colour</i>	<i>Number of buttons</i>	<i>Interface</i>	<i>Country version</i>	<i>EAN-Code</i>
G81-3000LRNFR-2	black	105	PS/2	France	4025112044403
G81-3000LRNGB-2	black	105	PS/2	UK-English	4025112044410
G81-3000LRNGR-0	light grey	105	PS/2	Greece	4025112053139
G81-3000LRNHU-0	light grey	105	PS/2	Hungary	4025112024245
G81-3000LRNIT-0	light grey	105	PS/2	Italy	4025112044427
G81-3000LRNNO-2	black	105	PS/2	Norway	4025112044434
G81-3000LRNRB-0	light grey	104	PS/2	US-English / Cyrillic	4025112010071
G81-3000LRNSF-0	light grey	105	PS/2	Sweden / Finland	4025112008979
G81-3000LRNSF-2	black	105	PS/2	Sweden / Finland	4025112044441
G81-3000LRNSL-0	light grey	105	PS/2	Slowenia	4025112010064
G81-3000LRNSL-2	black	105	PS/2	Slowenia	4025112050930
G81-3000LUNBE-0	light grey	105	USB	Belgium	4025112049071
G81-3000LUNCH-0	light grey	105	USB	Switzerland	4025112020629
G81-3000LUNDE-0	light grey	105	USB	Germany	4025112010149
G81-3000LUNDE-2	black	105	USB	Germany	4025112047299
G81-3000LUNES-0	light grey	105	USB	Spain	4025112010156
G81-3000LUNEU-0	light grey	104	USB	US-English / € - Symbol	4025112010163
G81-3000LUNFR-0	light grey	105	USB	France	4025112020612
G81-3000LUNFR-2	black	105	USB	France	4025112056482
G81-3000LUNGB-0	light grey	105	USB	UK-English	4025112022111
G81-3000LUNGB-2	black	105	USB	UK-English	4025112056086
G81-3000LUNIT-0	light grey	105	USB	Italy	4025112053313
G81-3000LUNRD-0	light grey	105	USB	Germany / Cyrillic	4025112036804
G81-3000LUNSF-0	light grey	105	USB	Sweden / Finland	4025112039973
G81-3000LUNSL-0	light grey	105	USB	Slowenia	4025112056093

Cherry GmbH
Cherrystraße
91275 Auerbach/Opf.
Germany

Phone: +49 9643 18-0
Internet: www.cherry.de
www.cherrycorp.com

Sales: +49 1805 243779 (01805-Cherry)
E-Mail: sales@cherry.de
Fax: +49 9643 18-1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2007 Cherry GmbH, Last update: 05.10.07_V07

