




.050" [1.27 mm] Contact Centers, Female Header, SMT with Posts- SFH Series Mates with SBH31 series (See opposite page)

SPECIFICATIONS

- Operating Temperature: -40°C to +105°C
- Processing Temperature: 230°C Max. for 60 seconds,
(260°C Max. for 10 seconds)
- UL Flammability Rating: 94V-0
- Contact Resistance: 20 milli Ohms Max.
- Current Rating: 1 Amp
- Dielectric Withstanding: 500 VAC
- Insulation Resistance: 5000 Megohms




PART NUMBER OPTIONS

SERIES	SFH31	- N	P	P	B	- D	10	- SP	- BK	COLOR
										BK = Black
INSULATOR MATERIAL										TERMINATION TYPE
N = Nylon										SP = Surface Mount with Guide Posts
CONTACT MATERIAL										NUMBER OF CONTACT POSITIONS
P = Phosphor Bronze										03 thru 50
CONTACT FINISH - RoHS Compliant										NUMBER OF ROWS
P = Gold Flash Overall										D = Dual Row
E = .000100" Pure Tin, Matte, Overall										CONTACT CENTERS
										B = .050" [1.27 mm]

DIMENSIONS For complete drawings, go to www.sullinscorp.com or e-mail techsupport@sullinscorp.com

Dimensions in [] are in millimeters, all others are in inches.



SURFACE MOUNT with Posts (SP)
Example P/N: SFH31-NPPB-D20-SP-BK