


LTA-Series




The LTA-Series Mini Tippette Snap-in rocker switches are illuminated, single pole and double-insulated. These AC rated switches are also suitable for low voltage DC applications. A variety of actuators, colors and terminations can be specified with ratings up to 20 amps.





Specifications

- Certifications*: UL, CSA
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon or Polycarbonate
- Bezel Material: Nylon


* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]




			
.069[1.75] DIA .250[6.35]	.156[3.96] DIA .375[9.52] .250[6.35]	.055[1.40] DIA .250[6.35] .187[4.74]	6.000[152.40] .500[12.70]
.250 TAB (Q.C.)	SOLDER LUG	.187 TAB (Q.C.)	INTEGRATED WIRE LEAD (no exposed conductors)


TERMINAL TYPE



PADDLE



SHORT PADDLE

MOUNTING HOLE
Panel Thickness:
.020[.508] min. to
.250[6.35] max.

LTA	20	1	-	T	R	-	B	-	/	125N	
SERIES	RATING	TERMINATION			ACTUATOR COLOR			LENS COLOR ^{2,3}			
LTA OFF-NONE-ON SINGLE POLE	10	5A 250VAC	0	SOLDER LUG	ROCKER			A	AMBER	LAMP VOLTAGE	
		10A 125VAC	1	.250 TAB (QC)	A AMBER			C	CLEAR		
		1/2HP 125-250VAC	3	.187 TAB (QC)	C CLEAR			G	GREEN		
	11	5A 250VAC	5	WIRE LEAD	G GREEN ³			LU	BLUE		
		10A 125VAC	ACTUATOR STYLE			R RED			R		RED
		5A (TUNGSTEN)	P	PADDLE	PADDLE ¹						
		125VAC L	PS	PADDLE - SHORT	B BLACK						
	20	10A 250VAC	T	LIGHTED ROCKER	W WHITE						
		15A 125VAC	BASE COLOR ¹								
		3/4HP 125-250VAC									
21	10A 250VAC							6V	6 VOLT/ INCANDESCENT		
	15A 125VAC							12V	12 VOLT/ INCANDESCENT		
22	10A 250VAC							18V	18 VOLT/ INCANDESCENT		
	15A 125VAC							24V	24 VOLT/ INCANDESCENT		
	20A 125-250VAC H							28V	28 VOLT/ INCANDESCENT		
	3/4HP 125-250VAC							125N	125 VOLT/ NEON		
								250N	250 VOLT/ NEON		

NOTES:

Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "BEZEL" to the end of the catalog number. (ex.) LTA201-TR-B/12V/BEZEL
Imprinting is available. Please specify when ordering.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

¹ Custom colors are available. Consult factory.

² Neon lamps (125 volt or 250 volt) not recommended with green or blue colored indicators.

³ Specify lens color only if actuator style is P or PS.