













NOTES:

1. USE #4 TYPE "B" THREAD FORMING SCREWS X .25 [6.3] LONG TO MOUNT CIRCUIT CARD ASSEMBLY.
2. RECOMMENED ASSEMBLY SCREW TORQUE SETTING IS 5 INCH-POUNDS.
3. TO MAINTAIN IP67 RATING USE THE GASKET ONCE; IF OPENING UNIT TO SERVICE MUST REPLACE GASKET.



SECTION D-D

PC BOARD BOTTOM COVER  
MAX PCB SIZE, .063 TK

PCB BOARD (TOP COVER)  
MAX PCB SIZE, .063 TK

**PACNTEC®**  
1-610-361-4231

**ODNF43**

VISIT **PACNTEC®**  
ON THE WORLD WIDE WEB  
[www.pactecenclosures.com](http://www.pactecenclosures.com)

MATERIAL:  
POLYCARBONATE (HB)  
WITH UV STABILIZER

COLOR:  
LIGHT GRAY #332

INSERT AREAS ARE SECTIONS IN OUR TOOLS  
THAT CAN BE REMOVED AND REPLACED WITH  
CUSTOMER SPECIFIC DETAILS

SCALE: 1/1

|                |     |
|----------------|-----|
| DRAWING NUMBER | REV |
| 87138          | D   |