

## Cable driller - WG-D HF 10,2 BK - 3241102

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Cable drillers, for fast and tool-free bundling of conductors and cables, removable and reusable



The illustration shows a version of the product

### Key commercial data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 1      |
| Minimum order quantity               | 1000 1   |
| Weight per Piece (excluding packing) | 0.4 GRM  |
| Custom tariff number                 | 39269097 |
| Country of origin                    | Taiwan   |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 26.2 mm |
| Width (a)  | 10.2 mm |

#### Ambient conditions

|                                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                 | -40 °C ... 85 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Ambient temperature (assembly)                  | -10 °C ... 60 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Optimum ambient temperature (storage/transport) | 23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |

#### General

|                                         |               |
|-----------------------------------------|---------------|
| Color                                   | black         |
| Type                                    | Notched strip |
| Inflammability class according to UL 94 | V2            |

## Cable driller - WG-D HF 10,2 BK - 3241102

### Technical data

#### General

|            |                                |
|------------|--------------------------------|
| Components | free from silicone and halogen |
| Material   | PA 6.6                         |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140702 |
| eCl@ss 4.1 | 27140702 |
| eCl@ss 5.0 | 27140702 |
| eCl@ss 5.1 | 27140702 |
| eCl@ss 6.0 | 27140702 |
| eCl@ss 7.0 | 27140702 |
| eCl@ss 8.0 | 27140702 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000046 |
| ETIM 4.0 | EC000046 |
| ETIM 5.0 | EC000046 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11     | 27121703 |
| UNSPSC 12.01  | 27121703 |
| UNSPSC 13.2   | 27121703 |