



**SPECIFICATIONS**

RESISTANCE RANGE	100 TO 100K OHMS
RESISTANCE TOLERANCE	$\pm 5\%$
ACCURACY	$\pm 0.35\%$ OF VOLTAGE RATIO
REPEATABILITY	$\pm 0.02\%$ OR RESOLUTION OF POT
RESOLUTION	SEE POT SPECIFICATIONS
POWER RATING	2 WATTS
OPERATING TEMPERATURE	-30°C TO +85°C
TEMPERATURE COEFFICIENT	$\pm 20 \text{ PPM}/^\circ\text{C}$
URNS	10 (000 TO 999 COUNTS)
TERMINALS	GOLD PLATED LUGS OVER THE CENTER
LOCK	LOCK
HOUSING MATERIAL	HIGH TEMP. BLACK PLASTIC

**NOTES:**

1. USE ETI SYSTEMS POTENTIOMETERS MODEL MW20B OR MW22B.
2. POTENTIOMETERS MAY BE 3,5,10 TURNS.  
ALSO MULTIPLE GANGS.
3. DIAL AVAILABLE WITHOUT POT, ASK FOR DC27FL.
4. THREADS WILL ACCEPT PANEL THICKNESS OF 3/16 MAX.
5. SEE POTENTIOMETER CATALOG FOR ADDITIONAL SPECIFICATIONS.

\*MODEL WITH MW20B IS DC20.



THIS DOCUMENT CONTAINS PROPRIETARY DATA  
OF POLARIS INDUSTRIAL ENTERPRISES, INC. NO  
DISCLOSURE, REPRODUCTION, OR USE OF ANY  
PART THEREOF MAY BE MADE EXCEPT BY  
WRITTEN PERMISSION.



ETI

SYSTEMS

CARLSBAD

CALIFORNIA

DC22

**TOLERANCES**

XX =  $+\text{-} .010$ " FRACT. =  $+\text{-} 1/64$ "  
XX =  $+\text{-} .005$ " ANGLES =  $+\text{-} 1/2$ "

ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

**TITLE**

POT/DIAL  
COMBINATION

**SCALE**

NONE  
DATE: 4-5-88  
BY: BY

**APPRV'D BY**

APP'R'D BY  
CODE IDENT:  
19477

**PART NO.**

DC22

REV.	BY	DATE	PART NO.
			DC22

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETI Systems](#):

[DC22-10-10K](#) [DC22-10-1K](#) [DC22-10-2K](#) [DC22-10-5K](#) [DC22-SB-10-10K](#) [DC22-10-100K](#)