


Pin Header 3,00 mm

Series

435



Rated current	5,0 A
Rated voltage	250 V _{RMS} / V _{DC}
Withstand voltage	1500 V _{RMS} for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch

3,00

termination







contact size

□ 0,64

max. pincount

024

Variation



Positioning peg:
1 = With peg

Plating:
T = Sn





Variation (1,2,3,4)

No. of contacts

Positioning peg

Plating contact

PCB Layout



Order code:

435-2-2-2-1-T-KS0

Mating series
see page

433
6-13



www.mpe-connector.de