

QRC series S9-M Socket for miniature 4 pole relay C9-...

Type **S9-M**
4-pole, 2 level
Integrated clip and marking label


Rated current **6 A**

Specifications


Rated load 6 A/250 V
Insulation Test voltage V rms/ 1 min
– All terminals/DIN rail 2,5 kV
– Terminal/terminal 2,5 kV
Cross-section of connecting wire
– Single-wire 4 mm² or 2 x 2,5 mm²
– Multi-wire 22 - 14 AWG
Max. screw torque 1,2 Nm
Screw dimensions M3, Pozi, slot
Integrated retaining clip/plastic for relay series C9
Labelling space detachable
Connection label 1...14; DIN/EN
Mounting DIN rail TS35 or mounting plate
Ambient temperature operation/storage -40 (no ice)...60 °C /-40 ... 80 °C

Socket for 4 poles, QRC relays




C9-A, C9-E, C9-R



Connection diagram



Dimensions [mm]



Technical approvals, conformities



EN 60947-1, EN 61810-5